



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



24FP4750C 40W 2X4 Led Flat Panel 50K

Cooper Lighting Solutions

Catalog Number	24FP4750C
Manufacturer	Cooper Lighting Solutions
Description	FP Series 2X4 Led Recessed Flat Panel, 4700 LM, 5000K, 80CRI, 0-10V Dimming Driver
Weight per unit	25.8 (lbs/each)
Product Category	Led Surface General Purpose Li

Features

amperage rating	0.145@277V A
Lamp Type	INCANDESCENT LANDSCAPE LIGHT FIXTURE, ECLIPSE TYPE; ALUMINUM MATERIAL; 4.5 INCH W X 18.5 INCH H SIZE; TEXTURED ARCHITECTURAL BRONZE FINISH; UL (CANADA AND US), CSA, ETL (US) APPROVAL; 8 INCH IN-GROUND STAKE, 18 INCH STEM MOUNTING
Voltage Rating	120/277 VAC
Wattage	40 W

Dimensions and Weight

Height	50.438 in
Length	50.813 in
Width	3.125 in

Descriptions

Description	40W 2X4 LED FLAT PANEL 50K
extra long description	ETNCL 24FP4750C 2X4 FPANEL 4700L, 5
Long Description	FP Series 2x4 LED recessed flat panel, 4700 LM, 5000K, 80CRI, 0-10V dimming driver
Product Type	2X4 Fpanel 4700L, 50K, 0-10V
Special Features	Ultra thin 1.75" height fits shallow plenums with room to spare

Manufacturer Information

Brand	METALUX COMMERCIAL
GTIN	00080083801503
Manufacturers Part Number	24FP4750C
sub brand	Fpanel LED Panel Series
UPC	080083801503

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	RECESSED



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 25.79

Uses, Certifications, and Standards

Application lighting

Mounting Recessed