



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



25023020 Galvanized Nipple

Conduit Pipe Products

| | |
|------------------|--|
| Catalog Number | 25023020 |
| Manufacturer | Conduit Pipe Products |
| Description | Conduit Pipe 25023020 Phoenix Conduit Nipple, Steel, Galvanized, 10 In Length, Trade Size: 3 In, 3-1/2 In Outside Diameter, Flexibility: Rigid, NPT, C/Us UI Listed, Csa Certified, Ansi B1.20.1 |
| Weight per unit | 4.9 (lbs/each) |
| Product Category | Steel |

Features

| | |
|------------------|----------|
| connection | 31276 |
| Material | Steel IN |
| outside diameter | 3.5 in |

Material, Color, and Finish

| | |
|--------|------------|
| Finish | Galvanized |
|--------|------------|

Dimensions and Weight

| | |
|--------|------|
| Length | 10 A |
|--------|------|

Descriptions

| | |
|------------------|--|
| Description | GALVANIZED NIPPLE |
| Long Description | Conduit Pipe 25023020 Phoenix Conduit Nipple, Steel, Galvanized, 10 IN Length, Trade Size: 3 IN, 3-1/2 IN Outside Diameter, Flexibility: Rigid, NPT, C/US UL Listed, CSA Certified, ANSI B1.20.1 |
| Product Type | 3 X 10 Cond Nip Gal |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | Conduit Pipe Products |
| GTIN | 00782172006188 |
| Manufacturers Part Number | 25023020 |
| sub brand | Phoenix |
| UPC | 782172006188 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | DIECAST EMT FITTINGS |
| Type | Conduit Nipple |

Trade Size

| | |
|------------|------|
| Trade Size | 3 in |
|------------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 4.92 |

Uses, Certifications, and Standards

| | |
|----------|---|
| standard | C/US UL Listed, CSA Certified, ANSI B1.20.1 |
|----------|---|