



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



257DCI2 3" Diecast Emt Insulated Concrete Tight Conn *Bridgeport Fittings*

| | |
|------------------|---|
| Catalog Number | 257DCI2 |
| Manufacturer | Bridgeport Fittings |
| Description | Connector, Compression, Zinc Die Cast, 105 Degree C Insulated Throat, Size 3 Inch |
| Weight per unit | 2.0 (lbs/each) |
| Product Category | Die Cast Insulated Straight CO |

Features

| | |
|----------------|------------------|
| Connector Type | Compression |
| insulation | Insulated Throat |
| media | Yes |

Material, Color, and Finish

| | |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

Dimensions and Weight

| | |
|------|---|
| Size | 3 |
|------|---|

Descriptions

| | |
|------------------------|---|
| Description | 3" DIECAST EMT INSULATED CONCRETE TIGHT CONN |
| extra long description | BPT 257-DCI2 3" COMP. CONN. INS. |
| Features | Think Orange: Zinc Advantage –Error-free Performance – meets same stringent UL tests as steel. Bridgeport zinc EMT fittings set the standard for EMT. |
| Long Description | Connector, Compression, Zinc Die Cast, 105 Degree C Insulated Throat, Size 3 Inch |
| Product Type | 3" Comp. Conn. Ins. |
| Special Features | Concrete-Tight |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747162571 |
| Manufacturers Part Number | 257-DCI2 |
| UPC | 781747162571 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | DIECAST EMT FITTINGS |
| Type | CONNECTOR |

Trade Size

| | |
|------------|---|
| Trade Size | 3 |
|------------|---|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|----|
| Carton | 12 |
| Weight Per each | 2 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Used to join steel EMT to box or enclosure. Concrete-tight. 2 1/2" thru 4" suitable for use with Steel EMT. Insulator rated 105°C. 2-1/2" through 4" also listed for use with Steel and Aluminum Rigid Conduit. |
| standard | cULus |