



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 26242W Decor Duplex Recept 15A 125V S-Wire W

*Pass & Seymour/Legrand*

Catalog Number	26242W
Manufacturer	Pass & Seymour/Legrand
Description	Heavy-Duty Decorator Spec Grade Duplex Receptacle Side Wire 15A 125V
Weight per unit	0.1950 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	15
connection	Side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Commercial, Indoor
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Height	3.813
Width	.833



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	DECOR DUPLEX RECP 15A 125V S-WIRE W
extra long description	P&S 26242W DECO DUP RECEP 15A 125V
Long Description	Heavy-Duty Decorator Spec Grade Duplex Receptacle Side Wire 15A 125V
Product Type	Deco Dup Recep 15A 125V S-Wire W
Special Features	Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body. One-piece, brass, triple-wipe power contacts for lasting retention. Heavy-duty compact design for easier installation and long lasting performance. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face. Terminal compartments isolated from each other for positive conductor containment. Side wire accepts #14 - #10 AWG solid or stranded w

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007784411
Manufacturers Part Number	26242-W
UPC	785007784411

## Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	100
Weight Per each	0.195

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-15R
standard	CULUS, UL498, cUL CSA