



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



273520 M18 Work Light

Milwaukee Electric Tool

Catalog Number	273520
Manufacturer	Milwaukee Electric Tool
Description	Powered By The M18™ Red Lithium™ Battery, The M18™ Cordless Led Work Light Has Over 600X The Life Of Conventional Incandescent Bulbs and Runs Up to 4X As Long. With A Sealed Aluminum Head to Provide Impact and Weather Resistance, Milwaukee® Provides A Limited Lifetime Led Warranty. An Integrated Hook Allows Hands-Free Use While A 135 Degree Rotating Head Allows The User to Easily Point The Light Beam At The Desired Work Area.
Weight per unit	0.9100 (lbs/each)
Product Category	Flashlights, Lanterns, Warning

Features

battery	Compact/XC High Capacity
Battery Size	Battery Packs
Battery Voltage	18
Belt Clip	No
bulb type	LED
charge time	0.5
lumens	160
Material	Rubber
Voltage Rating	18
Water Resistant	Yes

Material, Color, and Finish

color temperature	5600
-------------------	------

Dimensions and Weight

Size	8.500 IN Length
------	-----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	M18 WORK LIGHT
extra long description	MILW 2735-20 18volt Li-Ion LED Work
Features	Milwaukee Tool is committed to protecting our users's investments by providing high performing, trade-focused solutions that are fully compatible with M18™ REDLITHIUM™ batteries. The M18™ system has over 200 performance-driven solutions, and growing!
Long Description	Powered by the M18™ Red Lithium™ battery, the M18™ cordless LED work light has over 600X the life of conventional incandescent bulbs and runs up to 4X as long. With a sealed aluminum head to provide impact and weather resistance, Milwaukee® provides a limited lifetime LED warranty. An integrated hook allows hands-free use while a 135 degree rotating head allows the user to easily point the light beam at the desired work area.
Product Type	18VOLT Li-Ion Led Worklight
Short Description	18volt Li-Ion LED Worklight
Special Features	Features: Sealed, Aluminum Head Impact And Weather Resistant; 160 Lumen Led Bright, White, Smooth Beam; 4X Run-Time Lasts Up To 12 Hours On One Charge; Integrated Hook Hands-Free Use; 135 DEG Rotating Head Aims Light At Work Space; Tool Weight: 1.800 LB

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242199143
Manufacturers Part Number	2735-20
UPC	045242199143

Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	LED

Packaging

Carton	1
Package	6
Weight Per each	0.91