



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 273520 M18 Work Light *Milwaukee Electric Tool*

Catalog Number	273520
Manufacturer	Milwaukee Electric Tool
Description	Powered By The M18™ Red Lithium™ Battery, The M18™ Cordless Led Work Light Has Over 600X The Life Of Conventional Incandescent Bulbs and Runs Up to 4X As Long. With A Sealed Aluminum Head to Provide Impact and Weather Resistance, Milwaukee® Provides A Limited Lifetime Led Warranty. An Integrated Hook Allows Hands-Free Use While A 135 Degree Rotating Head Allows The User to Easily Point The Light Beam At The Desired Work Area.
Weight per unit	0.9100 (lbs/each)
Product Category	Flashlights, Lanterns, Warning

### Features

battery	Compact/XC High Capacity
Battery Size	Battery Packs
Battery Voltage	18
Belt Clip	No
bulb type	LED
charge time	0.5
lumens	160
Material	Rubber
Voltage Rating	18
Water Resistant	Yes

### Material, Color, and Finish

color temperature	5600
-------------------	------

### Dimensions and Weight

Size	8.500 IN Length
------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	M18 WORK LIGHT
extra long description	MILW 2735-20 18volt Li-Ion LED Work
Features	Milwaukee Tool is committed to protecting our users's investments by providing high performing, trade-focused solutions that are fully compatible with M18™ REDLITHIUM™ batteries. The M18™ system has over 200 performance-driven solutions, and growing!
Long Description	Powered by the M18™ Red Lithium™ battery, the M18™ cordless LED work light has over 600X the life of conventional incandescent bulbs and runs up to 4X as long. With a sealed aluminum head to provide impact and weather resistance, Milwaukee® provides a limited lifetime LED warranty. An integrated hook allows hands-free use while a 135 degree rotating head allows the user to easily point the light beam at the desired work area.
Product Type	18VOLT Li-Ion Led Worklight
Short Description	18volt Li-Ion LED Worklight
Special Features	Features: Sealed, Aluminum Head Impact And Weather Resistant; 160 Lumen Led Bright, White, Smooth Beam; 4X Run-Time Lasts Up To 12 Hours On One Charge; Integrated Hook Hands-Free Use; 135 DEG Rotating Head Aims Light At Work Space; Tool Weight: 1.800 LB

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242199143
Manufacturers Part Number	2735-20
UPC	045242199143

## Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	LED

## Packaging

Carton	1
Package	6
Weight Per each	0.91