



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



287722 M18 Force Logic 750 MCM Dieless Crimper

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 287722 |
| Manufacturer | Milwaukee Electric Tool |
| Description | The M18™ Force Logic™ 750 MCM Dieless Crimper Is The Simplest Way to Crimp. This Crimper Utilizes An Industry-First Technology Called Auto Distance Control to Produce CULus Classified Connections Under UI 486A-B For #6 - 750 MCM Cu and Dual Rated Connectors For Seven Major Manufacturers (Anderson, Blackburn® Burndy, IlSCO, Panduit, Penn-Union and Thomas & Betts). Auto Distance Control Enables The Tool to Sense The Instant It Contacts The Connector Delivering Optimal Compression With A Single Crimp Across T |
| Weight per unit | 20.0 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|-------------------|---------|
| crimping capacity | 750 MCM |
|-------------------|---------|

Descriptions

| | |
|-------------|---|
| Description | M18 FORCE LOGIC 750 MCM DIELESS CRIMPER |
|-------------|---|

| | |
|------------------------|--------------------------------------|
| extra long description | MILW 2877-22 750 MCM Dieless Crimper |
|------------------------|--------------------------------------|

| | |
|----------|--|
| Features | Milwaukee Tool is committed to protecting our users's investments by providing high performing, trade-focused solutions that are fully compatible with M18™ REDLITHIUM™ batteries. The M18™ system has over 200 performance-driven solutions, and growing! |
|----------|--|

| | |
|------------------|---|
| Long Description | The M18™ Force Logic™ 750 MCM dieless crimper is the simplest way to crimp. This crimper utilizes an industry-first technology called auto distance control to produce cULus classified connections under UL 486A-B for #6 - 750 MCM Cu and dual rated connectors for seven major manufacturers (Anderson, Blackburn® Burndy, IlSCO, Panduit, Penn-Union and Thomas & Betts). Auto distance control enables the tool to sense the instant it contacts the connector delivering optimal compression with a single crimp across t |
|------------------|---|

| | |
|--------------|-------------------------|
| Product Type | 750 MCM Dieless Crimper |
|--------------|-------------------------|

Manufacturer Information

| | |
|-------|------------|
| Brand | Milwaukee® |
|-------|------------|

| | |
|------|----------------|
| GTIN | 00045242020706 |
|------|----------------|

| | |
|---------------------------|---------|
| Manufacturers Part Number | 2877-22 |
|---------------------------|---------|

| | |
|-----|--------------|
| UPC | 045242020706 |
|-----|--------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description POWER TOOLS

Packaging

Carton 1

Package 2

Weight Per each 20.021