



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 282820 M18 Brushless String Trimmer (Tool-Only)

*Milwaukee Electric Tool*

Catalog Number	282820
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee® M18™ Brushless String Trimmer Delivers More Clearing Power and A Larger Cutting Swath Than Battery-Powered Competitors. The Brushless Motor Was Built and Optimized Specifically For Trimming Applications and Provides Up to 6, 200 RPM. Paired With Redlink™ Intelligence and An M18™ Redlithium™ High Output™ Battery, The Trimmer Provides Efficient Power Delivery Allowing For Longer Run-Time. The Trimmer Features High and Low Speed Settings With A Variable Speed Trigger. High-Speed Provides The Pow
Weight per unit	11.9 (lbs/each)
Product Category	Tools & Testers

### Features

Battery Voltage	18
cutting width	16

### Material, Color, and Finish

Handle Material	Plastic
Housing Material	Reinforced Nylon



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	M18 BRUSHLESS STRING TRIMMER (TOOL-ONLY)
extra long description	MILW 2828-20 Brushless String Trimm
Features	Milwaukee Tool is dedicated to providing innovative solutions that make professionals in the outdoor trades more productive and safer throughout their day. The outdoor equipment on our M18™ systems is designed to withstand the demanding work of landscape maintenance, landscape construction and tree care professionals. By delivering full battery compatibility within each system operators can easily switch the batteries between different equipment to move to the next task without any of the frustrations of g
Long Description	The MILWAUKEE® M18™ Brushless String Trimmer delivers more clearing power and a larger cutting swath than battery-powered competitors. The brushless motor was built and optimized specifically for trimming applications and provides up to 6,200 RPM. Paired with REDLINK™ Intelligence and an M18™ REDLITHIUM™ HIGH OUTPUT™ battery, the trimmer provides efficient power delivery allowing for longer run-time. The trimmer features high and low speed settings with a variable speed trigger. High-speed provides the pow
Product Type	Brushless String Trimmer
Short Description	Brushless String Trimmer

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242572045
Manufacturers Part Number	2828-20
UPC	045242572045

## Taxonomies, Classifications, and Categories

Category Description	POWER TOOLS
----------------------	-------------

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight	9.1
Weight Per each	11.9