



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 29W76 Turnlok Conn IP67 30A 3PH 480V L1630R

*Pass & Seymour/Legrand*

Catalog Number	29W76
Manufacturer	Pass & Seymour/Legrand
Description	Locking Watertight Connector, 30AMP 3 480VOLT, Nema Configuration L16-30, Multipoint Sealing System Provides Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated.
Weight per unit	0.8300 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	30
Cord Type	12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max
Material	Rubber
Number of Wires	4.0
Phase	Three
Poles	3-way
Voltage Rating	480
Wire Size	12 - 6 AWG

### Material, Color, and Finish

Color	Yellow
-------	--------

### Descriptions

Description	TURNLOK CONN IP67 30A 3PH 480V L1630R
extra long description	P&S 29W76 TL CONN IP67 30A 3PH 480V
Long Description	Locking Watertight Connector, 30amp 3 480volt, NEMA Configuration L16-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.
Product Type	TL Conn IP67 30A 3PH 480V L1630R
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033007
Manufacturers Part Number	29W76
UPC	785007033007

### Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Locking Connector



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage ..... 30.0

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 0.83

## Uses, Certifications, and Standards

Application

High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors | Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings | Ideal for washdown areas — rated wa

environmental conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized

nema rating

L16-30R

standard

UL Listed, CSA Listed