



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2BLT440LADPLP840 2X4 Led BSKT Trof 40K 4000LM

Lithonia Lighting - Acuity

| | |
|------------------|---|
| Catalog Number | 2BLT440LADPLP840 |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | The 2 FT. X 4 FT. BLT Low-Profile Recessed Led Lay-In By Lithonia Lighting Is What You've Come to Expect From The Leader In Lighting. With Its Endless Options and Configurations, BLT Provides The Versatility You Need At A Value That Can'T Be Beat. With A Curved, Linear Center Element, The BLT Provides A Consistent Look and Performance Throughout The Entire Application and Replaces Fluorescent Fixtures to Optimize Led Savings. |
| Weight per unit | 17.8 (lbs/each) |
| Product Category | Led Recessed Architectural & S |

Features

| | |
|-------------------------------|--------------|
| average life | 60,000 |
| dimnable | Yes |
| Hardware | No |
| Lamp Included | Yes |
| Lamp Type | LED - Static |
| lumens | 4000 LM |
| Material | Steel |
| Maximum Operating Temperature | 25 |
| pallet quantity | 26 |
| Power Source | Hardwired |
| Shape | Rectangular |
| Voltage Rating | 120-277 |
| Warranty | 5 |
| Wattage | 31.7 |

Material, Color, and Finish

| | |
|-----------------------------|-------------|
| Color | White |
| color rendering index (cri) | 80 |
| color temperature | 4000 |
| Finish | Matte |
| Lens Color | WHITE |
| Lens Material | Acrylic |
| Style | Traditional |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

| | |
|--------|-----|
| Height | 3.5 |
| Length | 50 |
| Width | 25 |

Descriptions

| | |
|------------------------|---|
| Construction | New Construction,Remodel |
| Description | 2X4 LED BSKT TROF 40K 4000LM |
| extra long description | LITH 2BLT4 40L ADP LP840 Basket LED |
| Features | Design Select |
| Long Description | The 2 ft. x 4 ft. BLT low-profile recessed LED lay-in by Lithonia Lighting is what you've come to expect from the leader in lighting. With its endless options and configurations, BLT provides the versatility you need at a value that can't be beat. With a curved, linear center element, the BLT provides a consistent look and performance throughout the entire application and replaces fluorescent fixtures to optimize LED savings. |
| Product Type | Troffer |
| Special Features | The BLT Best-in-Value Low Profile LED luminaire features a popular center basket design that offers a clean, versatile style and volumetric distribution. High efficacy LED light engines deliver energy savings and low maintenance compared to traditional sources. An extensive selection of configurations and options make the BLT the perfect choice for many lighting applications including schools, offices and other commercial spaces, retail, hospitals and healthcare facilities. The low profile BLT design (2-3/ |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Lithonia Lighting |
| GTIN | 00190887470765 |
| Manufacturers Part Number | 2BLT4 40L ADP LP840 |
| UPC | 190887470765 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | Led Lighting |
| Type | Troffer |

Trade Size

| | |
|---------------|-----|
| aperture size | 2x4 |
|---------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight | 14.5 |
| Weight Per each | 17.75 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Clean Room, Education, Government, Healthcare, Hospitality, House of Worship, Offices & Banks, Patient Room, Retail |
| environmental conditions | Indoor |
| Mounting | Recessed |
| standard | CSADLC Premium |