



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



29W77 Turnlok Conn IP67 4W 30A 600V L1730R

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 29W77 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Locking Watertight Connector, 30AMP 3Y 600VOLT, Nema Configuration L17-30, Multipoint Sealing System Provides Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated. |
| Weight per unit | 0.8300 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|---|
| amperage rating | 30 |
| Cord Type | 12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max |
| Material | Rubber |
| Number of Wires | 4 |
| Phase | 1 |
| Poles | 3 |
| Voltage Rating | 600 |
| Wire Size | 12 - 6 |

Descriptions

| | |
|------------------------|--|
| Description | TURNLOK CONN IP67 4W 30A 600V L1730R |
| extra long description | P&S 29W77 TL CONN IP67 4W 30A 600V |
| Long Description | Locking Watertight Connector, 30amp 3Y 600volt, NEMA Configuration L17-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated. |
| Product Type | TL Conn IP67 4W 30A 600V L1730R |
| Special Features | Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation. |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007033731 |
| Manufacturers Part Number | 29W77 |
| UPC | 785007033731 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type | Locking Connector |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.83 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings Ideal for washdown areas — rated wa |
| environmental conditions | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized |
| nema rating | L17-30R |
| standard | UL Listed, CSA Listed |