



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 301362 Weatherproof Wire Conn, 62 Gray/Red, 1, 000/Box

*Ideal*

Catalog Number	301362
Manufacturer	Ideal
Description	Model 62 Gray-Red 1000 Box
Weight per unit	0.0120 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

Quantity	Box of 1000
----------	-------------

### Material, Color, and Finish

Color	Gray-Orange
-------	-------------

### Descriptions

Description	WEATHERPROOF WIRE CONN, 62 GRAY/RED, 1,000/BOX
extra long description	IDEAL 30-1362 WP MODEL 62, GRAY-RED
Features	100% Silicone-based sealant protects against moisture and corrosionUL Listed to 486G Sealed Twist-On Wire Connector for use in damp/wet locations or above-grade applicationsEasy to apply, pre-filled twist-on wire connectorsSwept wing design is built for comfort and efficiencyEliminates the need for heat-shrink or excessive tapingTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)For use in damp/wet location or above-grade applicationsConnected and protected.Designed specifically for above-grade, i
Long Description	MODEL 62 GRAY-RED 1000 BOX
Product Type	WP Model 62, Gray-Red, 1000 BX
Special Features	Hexagonal shape allows connectors to be applied with standard nutdriver. Silicone-based sealant protects against moisture and corrosion. Easy to apply pre-filled twist-on wire connectors

### Manufacturer Information

Brand	Ideal
GTIN	00783250756346
Manufacturers Part Number	30-1362
UPC	783250756346

### Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Model 62® Connector

### Availability

minimum qty	1000
-------------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1000
Weight Per each	0.012

## Uses, Certifications, and Standards

Application	Handles wire sizes from #18 to #8 AWG copper. Minimum of 2 #18 AWG. Maximum of 3 #10 AWG.
standard	UL Listed to 486D for use with damp/wet locations