



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30092J Greenie Grounding Wire Conn, 92 Green, 150/Jar

*Ideal*

Catalog Number	30092J
Manufacturer	Ideal
Description	Ideal, Grounding Wire Connector, Greenie, Twist-On, Number Of Conductors: 2 to 5, Conductor Range: 14 - 10 Awg, Min 2 - 14, Max 4-12, Color: Green, Material: Polypropylene, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell, Model Number: 92, Width: 29/32 In, Height: 1-5/32 In, Flammability Rating: UI 94V-2
Weight per unit	0.0080 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Polypropylene
Voltage Rating	600

### Material, Color, and Finish

Color	Green
-------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	GREENIE GROUNDING WIRE CONN, 92 GREEN, 150/JAR
extra long description	IDEAL 30-092J GREENIE GROUNDING 92,
Features	The Wing-Nut Wire Connector provides an easy, secure grip when connecting a wide range of wires. The specially designed contoured wings make for extra torque and quick work on any electrical job. The wide range, live-action spring is flexible enough to handle small combinations with ease but then expands to accept large combinations when you need it. It can also be reused on same size or larger combinations for quick and easy circuit changes and additions. The Wing-Nut also features a tough, copolymer, flam
Long Description	IDEAL, Grounding Wire Connector, Greenie, Twist-On, Number Of Conductors: 2 to 5, Conductor Range: 14 - 10 AWG, Min 2 - 14, MAX 4-12, Color: Green, Material: Polypropylene, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell, Model Number: 92, Width: 29/32 IN, Height: 1-5/32 IN, Flammability Rating: UL 94V-2
Product Type	Greenie Grounding 92, 150 Jar
Special Features	Complies With Federal Specification W-S-610E; Contoured Wings For Maximum Leverage; Features: Designed For Making Ground Connections And Bonding Non-Metallic Sheathed Cable; Flammability Rating: UL 94V-2; Height: 1-5/32 IN; Live-Action, Square-Wire Spring Provides Superior Grounding Connections; Model Number: 92; Tough, UL 94V-2 Flame-Retardant Shell; UL Listed To 467 And CSA Certified To C22.2 #188; Width: 29/32 IN

## Manufacturer Information

Brand	Ideal
GTIN	00783250541232
Manufacturers Part Number	30-092J
UPC	783250541232

## Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Twist-On

## Availability

minimum qty	150
-------------	-----

## Packaging

Carton	150
Package	900
Weight Per each	0.008



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Insulating or Joining 2 or more conductors .....
environmental conditions .....	Tough, UL 94V-2 Flame-Retardant Shell .....
standard .....	CSA Certified to C22.2 #188, UL Listed to 467, complies with .....
.....	Federal Specification W-S-610E, RoHS Compliant .....