



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



302412SDSS4 Encl 30X24X12 N4X SS4 HC, QTR TRN LTCH *Cooper B-Line/Cable Tray*

Catalog Number	302412SDSS4
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 30" Height, 12" Length, 24" Width, Nema 4X, Hinged Cover, SDSS4 Enclosure, Wall Mount, Medium Single Door, Thru Holes, Opt. External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket
Weight per unit	60.9 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

dimensions	12.0000 IN X 24.0000 IN X 30.0000 IN
Material	304 Stainless Steel
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	24.00 In Width X 12.00 In Depth X 30.00 In Height
------	---

Descriptions

Description	ENCL 30X24X12 N4X SS4 HC,QTR TRN LTCH
extra long description	B-LINE 302412-SDSS4 TYPE 4X SSL SGL
Features	Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series wall mounted panel enclosure,30" height,12" length,24" width,NEMA 4X,Hinged cover,SDSS4 enclosure,Wall mount,Medium single door,Thru holes,opt. external mounting feet,304 stainless steel,Seamless poured in-place gasket
Product Type	Type 4X SSL SGL-Solid Door Enc, 30X24X12
Special Features	Stainless 1/4 turn latches

Manufacturer Information

Brand	Eaton
GTIN	00782051093698
Manufacturers Part Number	302412-SDSS4
UPC	782051093698

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Wall mounted panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	60.89

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Other IT and Datacom - IT and Datacomm - Other Commercial / Institutional Buildings / Structures - Critical Power Utility - Substations, Utility Transmission and Distribution Datacenters - IT Space: CI and Hyper Converged Commercial / Institutional Buildings / Structures - Power Distribution and Controls Commercial / Institutional Buildings / Structures - Building Automation and Monitoring Commercial / Institutional Buildings / Structures - Commercial / Institutional
Mounting	WALL
nema rating	4X
standard	UL 50,NEMA,CSA C22.2.