



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



301032 In-Sure Push-In Wire Conn, 32 2-Port Red, 100/Box

Ideal

| | |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 301032 |
| Manufacturer | Ideal |
| Description | Push-In Wire Connector, Red Insulation Color, +221 °F Operating Temperature, 0.780 In Overall Length, 0.520 In Overall Width, 0.380 In Overall Height, 600 V (Building Wire);1000 V (Maximum Signs/Lighting Fixture), 0.44 LB |
| Weight per unit | 0.0040 (lbs/each) |
| Product Category | Electrical Fixture Conn (Nuts |

Features

| | |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| connection | 2 Ports |
| Voltage Rating | 600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures |
| Wire Size | #12 AWG - #20 AWG Solid, #12 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand) Stranded, #14 AWG - #18 AWG (19 Strand Or Less) Stranded (Tin Bonded) |
| Wire Type | Solid, Stranded, Stranded (Tin Bonded) |

Material, Color, and Finish

| | |
|-------|-----|
| Color | Red |
|-------|-----|

Dimensions and Weight

| | |
|------|----------------------------------------------------|
| Size | 0.780 IN Length X 0.520 IN Width X 0.380 IN Height |
|------|----------------------------------------------------|

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | IN-SURE PUSH-IN WIRE CONN, 32 2-PORT RED, 100/BOX |
| extra long description | IDEAL 30-1032 PUSH-IN 12AWG 2-PORT, |
| Features | Ergonomic design for easy grip and comfortable installationLow insertion force for fast and easy connectionsCompact size makes installation easyClear shell gives visual verification of connectionTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)Approved for bonding and grounding applicationsStrip, push, connect – the fastest way to make a connection.The In-Sure Push-In Wire Connector is perfect for residential, light commercial, lighting retrofit, and pre-fab wiring systems, or any other branch c |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Ideal |
| GTIN | 00783250693511 |
| UPC | 783250693511 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------|
| Category Description | WIRE NUTS |
| Type | Push-In |

Availability

| | |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 100 |
| Package | 1000 |
| Weight Per each | 0.004 |

Uses, Certifications, and Standards

| | |
|--------------------|------------------------------------------|
| standard | CSA C22.2 #188, 486C/467 UL Listed, RoHS |
| Temperature Rating | 105 DEG C Shell Rated |