




# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **30204 1G WP BX (3) 3/4HUBS Gry** *Mulberry Metal*

Catalog Number	30204
Manufacturer	Mulberry Metal
Description	Mulberry; Weatherproof Box; Single Gang; Number Of Outlet: 3; Material: Heavy Duty Die-Cast Aluminum; Size: 3/4 In Hub; Color: Gray; Cubic Capacity: 19 In; Outlets/Location: (1) Each End, (1) Back; Lugs: No
Weight per unit	N/A
Product Category	Bar Hangers & Outlet Box Accy.

### Features

Material	HEAVY DUTY DIE-CAST ALUMINUM
number of outlet	3

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	3/4 IN Hub
------	------------

### Descriptions

Description	1G WP BX (3) 3/4HUBS GRY
extra long description	MULB 30204 WP ALUM BOX 3H-3/4"
Long Description	Mulberry; Weatherproof Box; Single Gang; Number Of Outlet: 3; Material: Heavy Duty Die-Cast Aluminum; Size: 3/4 IN Hub; Color: Gray; Cubic Capacity: 19 IN; Outlets/location: (1) Each End, (1) Back; Lugs: No
Product Type	WP Alum Box 3H-3/4"
Special Features	0.094 IN Thick, With Powder Finish;2.750 IN X 4.500 IN X 2.000 IN Deep;Features: All 1-Gang Boxes Available With Or Without Attached Swivel Lugs;Ground Screw And 2 Close-Up Plugs Supplied With Each Box;Lugs: No;Outlets/location: (1) Each End, (1) Back;Pre-Tapped Ground Screw Hole

### Manufacturer Information

Brand	Mulberry
GTIN	00095327302043
Manufacturers Part Number	30204
UPC	095327302043

### Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	SINGLE GANG



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0

## Uses, Certifications, and Standards

Application	For All Indoor And Outdoor Damp Or Wet Locations
standard	UL Listed, CSA, Federal Specification AA-50563