



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



306064 Underground Wire Conn, 60/64, 5 Of Each, 10/Card

Ideal

| | |
|------------------|--------------------------------|
| Catalog Number | 306064 |
| Manufacturer | Ideal |
| Description | 60 64 Undergrd 10 Clam |
| Weight per unit | 0.0200 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|----------|------------|
| Quantity | Card of 10 |
|----------|------------|

Material, Color, and Finish

| | |
|-------|------|
| Color | Gray |
|-------|------|

Descriptions

| | |
|------------------------|---|
| Description | UNDERGROUND WIRE CONN, 60/64, 5 OF EACH, 10/CARD |
| extra long description | IDEAL 30-6064 60 64 UNDERGRD COMBO, |
| Features | 100% Silicone-based sealant protects against moisture and corrosionUL Listed to 486G Sealed Twist-On Wire Connector for use in damp/wet locations or above-grade applicationsEasy to apply, pre-filled twist-on wire connectorsExpanding, live-action square-wire spring for fast, secure and long-lasting connectionsDeep skirt provides superior moisture resistance to protect connectionsTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)For use in damp/wet location or direct burial/below-grade applications |
| Long Description | 60 64 UNDERGRD 10 CLAM |
| Product Type | 60 64 Undergrd Combo, 10 Clam |
| Special Features | Smallest wet location/direct burial connector with widest wire range. Non-hardening sealant completely seals out moisture to protect fungus and corrosion. Sealant is stable down to -40° C. Flame-retardant Shell |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250758173 |
| Manufacturers Part Number | 30-6064 |
| UPC | 783250758173 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------------|
| Category Description | WIRE NUTS |
| Type | Model 60® & Model 64® Combo Pack |

Availability

| | |
|-------------|----|
| minimum qty | 10 |
|-------------|----|

Packaging

| | |
|-----------------|------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.02 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Model 60® Handles wire sizes from #20 to #10 AWG copper. Model 60® Minimum of 1 #20 with 1 #18. Model 60® Maximum of 2 #12 & 1 #10 AWG. Model 64® Handles wire sizes from #18 to #8 AWG copper. Model 64® Minimum of 2 #18 AWG. Model 64® Maximum of 2 #10 AWG |
| standard | UL Listed & CSA certified |