



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30826 1800W 120V Photo Cell *Mulberry Metal*

Catalog Number	30826
Manufacturer	Mulberry Metal
Description	Mulberry; Photo Control; Direct Wire-In; Supply Voltage: 120 V; Timing Range: 15 S; Connection: 1/2-14 In Threaded Stem; Mounting: Fixed or Swivel; Enclosure: High Impact Polycarbonate; Operating Temperature: -40 to 158 Deg F; Tungsten Watts: 1800 WTT; Tungsten Amps: 15 Amp; Ballast Watts: 1000 WTT; Ballast Amps: 8.3 Amp
Weight per unit	0.3800 (lbs/each)
Product Category	Lighting Photocells

### Features

connection	1/2-14 IN Threaded Stem
supply voltage	120
Timing Range	15

### Descriptions

Description	1800W 120V PHOTO CELL
extra long description	MULB 30826 120V SWIVEL PHOTO CONTRO
Long Description	Mulberry; Photo Control; Direct Wire-In; Supply Voltage: 120 V; Timing Range: 15 S; Connection: 1/2-14 IN Threaded Stem; Mounting: Fixed Or Swivel; Enclosure: High Impact Polycarbonate; Operating Temperature: -40 To 158 DEG F; Tungsten Watts: 1800 WTT; Tungsten Amps: 15 AMP; Ballast Watts: 1000 WTT; Ballast Amps: 8.3 AMP
Product Type	120V Swivel Photo Control
Special Features	Features: High Impact Polycarbonate Housing; Turn On Between 1 And 5 Foot Candles; Turn On/Turn Off Ratio 1 To 3; Single-Pole, Single-Throw Switching; Minimum Time Delay 15 Seconds; Contact Position At Night Normally Closed; External Slide Clip Allows Light Level Adjustment; With 2 IN - 14 Threaded Stem Fits 2 IN Knockout; With 6 IN Color-Coded Lead Wire; Temperature Range -40 Deg F (-40 Deg C) To 158 Deg F (70 Deg C); Tungsten Watts: 1800 WTT; Tungsten Amps: 15 AMP; Ballast Watts: 1000 WTT; Ballast Amps:

### Manufacturer Information

Brand	Mulberry
GTIN	00095327308267
Manufacturers Part Number	30826
UPC	095327308267



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Commercial dimmers, motion sensors, & photo cells
Type	Direct Wire-In

## Packaging

Carton	1
Package	10
Weight Per each	0.38

## Uses, Certifications, and Standards

Application	For Wet Locations
Enclosure	High Impact Polycarbonate
Mounting	Fixed Or Swivel
Operating Temperature standard	-40 to 158 UL Listed, CSA Certified