

VARI-BIT® STEP DRILL BITS

Drills Fast, Clean, Round Holes



LENOX® VARI-BIT® Kits



4 Piece (1/8"–1")
Product No.
30926-VBK-4
 4 sizes: VB1, VB2, VB7,
 VB8. Instruction sheet.
 Plastic case.



4 Piece (1/8"–1-3/8")
Product No.
30929-30/929
 4 sizes: VB1, VB3, VB8,
 VB12. Instruction sheet.
 Plastic case.



4 Piece (3/16"–1-1/8")
Product No.
30928-VBKE
 4 sizes: VB3, VB6, VB8,
 VB11. Instruction sheet.
 Plastic case.



6 Piece (1/8"–1-1/8")
Product No.
30927-VBKA-6
 6 sizes: VB1, VB2, VB6,
 VB7, VB8, VB11.
 Instruction sheet.
 Plastic case.



3 Piece (1/8"–1")
Product No.
30889-889
 3 sizes: VB1, VB2, VB3.
 Instruction sheet.
 Plastic case.

THE LENOX® ADVANTAGE™

- **Accurate, burr-free holes**
Patented two flute design cuts fast, clean, round holes.
- **Starts on contact**
Split point design for faster penetration and less walking.
- **Long tool life**
Steam oxide coating adds durability. Enhanced flute design removes chips rapidly, ensuring longer tool life.

Specifications (1 per pack)

U.S. PATENT NO. 4582458

| Product Number | Photo | Hole Sizes (Inches) | Chuck Size (Inches) | Unibit® | Klein Unibit® |
|----------------|-------|---|---------------------|------------|---------------|
| 30881-VB1 | | 1/8, 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 13/32, 7/16, 15/32, 1/2 | 1/4 | 1 | 1-59001 |
| 30882-VB2 | | 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1 | 3/8 | 20 | 2-59002 |
| 30883-VB3 | | 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4 | 3/8 | 3 | 3-59003 |
| 30884-VB4 | | 3/16, 1/4, 5/16, 3/8, 7/16, 1/2 | 1/4 | 2 | 5-59005 |
| 30886-VB6 | | 3/8, 1/2 | 1/4 | 10, 12* | 7-59007 |
| 30887-VB7 | | 7/8 (for 1/2" conduit) | 3/8 | 11 | 8-59008 |
| 30908-VB8 | | 3/16, 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8 | 3/8 | 4 | 14-590014 |
| 30909-VB9 | | 7/8, 1-1/8, 1-7/32 | 3/8 | 11, 13, 14 | 59011 |
| 30888-VB11 | | 7/8, 1-1/8 (for 1/2" and 3/4" conduit) | 3/8 | 13** | 11-590011 |
| 30912-VB12 | | 7/8, 1-1/8, 1-7/32, 1-1/4, 1-3/8 | 3/8 | none | none |
| 30925-VBX8 | | Extension 8" Fits 3/8" drill chuck & larger. 1 per clam | | | |

* LENOX® VARI-BIT® #6 combines Unibit® #10 & #12.

** Unibit® #13 has 1-1/8" step only. VARI-BIT® has both 7/8" & 1-1/8".