



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35083 Twist-A-Nut Conduit Deburring Tool, Slotted Tip

Ideal

| | |
|------------------|--|
| Catalog Number | 35083 |
| Manufacturer | Ideal |
| Description | Ideal, Conduit Deburring Tool, Twist-A-Nut, Slotted Tip, Warranty: Lifetime Guarantee |
| Weight per unit | 0.3333 (lbs/each) |
| Product Category | Tool Kits |

Descriptions

| | |
|------------------------|---|
| Description | TWIST-A-NUT CONDUIT DEBURRING TOOL, SLOTTED TIP |
| extra long description | IDEAL 35-083 TWIST-A-NUT CONDUIT DE |
| Features | Deburrs inside and outside edges of 1/2 in., 3/4 in. and 1 in. thin wall conduit Hooded tip tightens EMT fitting set screws without slipping Square tip "seats" much more quickly on fitting screws than slotted version Head removes and is interchangeable with IDEAL 7-in-1 Twist-a-Nut Screwdriver shaft (#35-908) Head can be used at low speed setting in drill or cordless screwdriver |
| Long Description | IDEAL, Conduit Deburring Tool, Twist-A-Nut, Slotted Tip, Warranty: Lifetime Guarantee |
| Product Type | Twist-A-Nut Conduit Deburrer |
| Special Features | Features: Deburrs Inside And Outside Edges Of 1/2, 3/4, And 1 IN Thin Wall Conduit; Hooded Tip Tightens Emt Fitting Set Screws Without Slipping; Removable Head Interchangeable With Ideal 7-In-1 Twist -A-Nut Screwdriver Shaft (35-908); Head Can Be Used In Drill Or Cordless Screwdriver; Universal Wire-Nut Wrench In Handle End Eases Installation Of Twist-On Connectors; Lifetime Guarantee (Excludes Blades); Warranty: Lifetime Guarantee |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250350834 |
| Manufacturers Part Number | 35083 |
| UPC | 783250350834 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | HAND TOOLS |
| Type | SLOTTED TIP |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Weight Per each | 0.3333 |