



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35196 Phillip Screwdriver 5/16 X 6" X #3

Ideal

Catalog Number	35196
Manufacturer	Ideal
Description	Ideal, Screwdriver, Phillips, Phillips Head Screws, Tip Size: #3, Overall Length: 11 In, Shank Length: 6 In, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Blade Finish: Nickel-Chrome Plating, Tip Type: Phillips, Shank Size: #3 In, Warranty: Lifetime Guarantee
Weight per unit	0.4333 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Type	Cushioned Rubber Grip
Shank Length	6
Tip Size	#3
tip type	Phillips

Material, Color, and Finish

Blade Material	Chrome Vanadium Steel
----------------	-----------------------

Dimensions and Weight

Overall Length	11
----------------	----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	PHILLIP SCREWDRIVER 5/16 X 6" X #3
extra long description	IDEAL 35-196 PHILLIP SCREWDRIVER 5
Features	The Phillips Cushioned-Grip Screwdrivers boast a rugged, nickel-chrome plating, great for corrosion resistance. These screwdrivers offer several different tip sizes and feature FastFinder handles that quickly help the user identify the tip type on the end of the handle. The cushion-grip handles are resistant to oil, gas and water, helping to prevent slippage for greater torque and superior comfort. For easy identification, the handle ends are color-coded.
Long Description	IDEAL, Screwdriver, Phillips, Phillips Head Screws, Tip Size: #3, Overall Length: 11 IN, Shank Length: 6 IN, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Blade Finish: Nickel-Chrome Plating, Tip Type: Phillips, Shank Size: #3 IN, Warranty: Lifetime Guarantee
Product Type	Phillip Screwdriver 5 16X6"X 3
Special Features	Features: Vapor-Blasted Tip Prevents Plate Chipping; Nickel-Chrome Plating For Corrosion Resistance; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grip; Lifetime Guarantee; Identification Mark On Ends; Shank Size: #3 IN; Warranty: Lifetime Guarantee

Manufacturer Information

Brand	Ideal
GTIN	00783250351961
Manufacturers Part Number	35-196
UPC	783250351961

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Phillips, Phillips Head Screws

Packaging

Carton	1
Weight Per each	0.4333