



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35291 1/4" Nutdriver *Ideal*

Catalog Number	35291
Manufacturer	Ideal
Description	Ideal, Nutdriver, Nutmaster, Drive Size: 1/4 In, Shank Length: 3-1/4 In, Shank Type: Hollow, Handle Color: Red, Shank Finish: Nickel Chrome Plated, Warranty: Lifetime Guarantee, Handle Type: Cushioned Rubber Grip
Weight per unit	0.2333 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Drive Size	1/4
Shank Length	3.25
Shank Type	Hollow

Material, Color, and Finish

Handle Color	Red
--------------	-----

Descriptions

Description	1/4" NUTDRIVER
extra long description	IDEAL 35-291 Nutdriver,Ideal,Nutmas
Features	Nut Drivers are nickel-chrome plated to resist corrosion and have long, hollow shanks that handle longer bolts, making them ideal for deep electrical boxes. The drivers are made in various colors and offer cushioned rubber grip handles for added torque and comfort.
Long Description	IDEAL, Nutdriver, Nutmaster, Drive Size: 1/4 IN, Shank Length: 3-1/4 IN, Shank Type: Hollow, Handle Color: Red, Shank Finish: Nickel Chrome Plated, Warranty: Lifetime Guarantee, Handle Type: Cushioned Rubber Grip
Product Type	Nutdriver, Ideal, Nutmaster, DRV SZ: 1/4 In, 3-1/4 In Shank Len,
Special Features	3-1/4 IN Long Shank;Cushioned Rubber Grip;Features: Color Code - Red;Handle Type: Cushioned Rubber Grip;Lifetime Guarantee;Long, Hollow Shank Handles Longer Bolts;Nickel Chrome Plated To Resist Rust And Corrosion;Shank Finish: Nickel Chrome Plated;Warranty: Lifetime Guarantee

Manufacturer Information

Brand	Ideal
GTIN	00783250352913
Manufacturers Part Number	35-291
UPC	783250352913



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description HAND TOOLS

Packaging

Carton 1

Weight Per each 0.2333

Uses, Certifications, and Standards

Application For 1/4 IN Nuts