



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35166 RD Shank Screwdriver, 5/16 X 6"

Ideal

| | |
|------------------|--|
| Catalog Number | 35166 |
| Manufacturer | Ideal |
| Description | Ideal, Screwdriver, Heavy-Duty, Slotted, Keystone Tip, Tip Size: 1/4 In, Overall Length: 11 In, Shank Length: 6 In, Shank Shape: Round, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Tip Type: Keystone, Shank Size: 5/16 In, Warranty: Lifetime Guarantee |
| Weight per unit | 0.3833 (lbs/each) |
| Product Category | Pliers, Wrenches, Saw, Pouches |

Features

| | |
|--------------|-----------------------|
| Handle Type | Cushioned Rubber Grip |
| Shank Length | 6 |
| Shank Shape | Round |
| Tip Size | 1/4 |
| tip type | Keystone |

Material, Color, and Finish

| | |
|----------------|-----------------------|
| Blade Material | Chrome Vanadium Steel |
|----------------|-----------------------|

Dimensions and Weight

| | |
|----------------|----|
| Overall Length | 11 |
|----------------|----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | RD SHANK SCREWDRIVER, 5/16 X 6" |
| extra long description | IDEAL 35-166 RD SHANK SCREWDRIVER, |
| Features | The Heavy-Duty Round Shaft Keystone Cushioned-Grip Screwdriver has a cushion-grip handle that is resistant to oil, gas and water, and helps to prevent slippage for greater torque and superior comfort. They feature nickel chrome plated vanadium steel heavy-duty square shanks and offer wrench-assisted turning. It has a cross-ground black oxide finish tip to provide a precise and secure fit in the screw slot. The handle ends are all color-coded for quick and easy identification. Screwdriver meets ASTM F1505-0 |
| Long Description | IDEAL, Screwdriver, Heavy-Duty, Slotted, Keystone Tip, Tip Size: 1/4 IN, Overall Length: 11 IN, Shank Length: 6 IN, Shank Shape: Round, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Tip Type: Keystone, Shank Size: 5/16 IN, Warranty: Lifetime Guarantee |
| Product Type | RD Shank Screwdriver, 5 16X6" |
| Special Features | Features: Larger Shank For Heavy-Duty Applications; Identification Mark On Ends; Vapor-Blasted Tip Prevents Plate Chipping; Precision Ground Tip Provides Secure Fit In Screw Slot; Square-Shank Models Offer Wrench-Assisted Turning; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grips; Shank Size: 5/16 IN; Warranty: Lifetime Guarantee |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250351664 |
| Manufacturers Part Number | 35-166 |
| UPC | 783250351664 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | HAND TOOLS |
| Type | Heavy-Duty, Slotted, Keystone Tip |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Weight Per each | 0.3833 |