



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 35260 Heavy Duty Hacksaw, Combination

*Ideal*

Catalog Number	35260
Manufacturer	Ideal
Description	Ideal, Hacksaw, Dual-Purpose, Heavy-Duty, Overall Length: 16 In, Teeth Per Inch: 24 Tpi, Blade Size: 12 In, Blade Material: Bi-Metal
Weight per unit	1.6 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

### Features

Blade Size	12
Teeth per Inch	24

### Material, Color, and Finish

Blade Material	Bi-Metal
----------------	----------

### Dimensions and Weight

Overall Length	16
----------------	----

### Descriptions

Description	HEAVY DUTY HACKSAW, COMBINATION
extra long description	IDEAL 35-260 HACKSAW(COMBINATION)
Features	The dual purpose hacksaw measures 16 in. length and is constructed from Bi-metal material for long lasting durability, strength and flexibility. Standard, jab/hacksaw includes 12 in. x 24 TPI bi-metal blade that can be adjusted to 55° angle for easy flush cutting. Rugged frame allows lightweight rigidity and exceptional control when in use. It is designed such that it stores up to nine extra blades for user convenience and can also be used as conventional hacksaw or as jab saw to enlarge holes.
Long Description	IDEAL, Hacksaw, Dual-Purpose, Heavy-Duty, Overall Length: 16 IN, Teeth Per Inch: 24 TPI, Blade Size: 12 IN, Blade Material: Bi-Metal
Product Type	Hacksaw(Combination)
Special Features	Features: Use As Conventional Hacksaw Or As Jab Saw To Enlarge Holes; Rugged Frame Provides Lightweight Rigidity And Exceptional Control; Stores Up To Nine Extra Blades; Includes 12 Inch X 24 Teeth Per Inch Bi-Metal Blade; Blades Can Be Adjusted To 55 Degree Angle For Flush Cutting; Cushioned Ergonomic Grip For Performance And Comfort



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Ideal
GTIN	00783250352609
Manufacturers Part Number	35-260
UPC	783250352609

## Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Dual-Purpose, Heavy-Duty

## Packaging

Carton	1
Weight Per each	1.6

## Uses, Certifications, and Standards

Application	For Flush Cutting, Use As Conventional Hacksaw Or As Jab Saw To Enlarge Holes
standard	RoHS