



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35988 Ratch-A-Nut 9-In-1 Screwdriver

Ideal

| | |
|------------------|--|
| Catalog Number | 35988 |
| Manufacturer | Ideal |
| Description | Ratch-A-Nut 9-In-1 Screwdriver, Textured, Ergonomic, Slip Resistant Comfort-Grip Handle, Santoprene Handle, Chrome Vanadium Blade, Includes: 1/4 In and 3/16 In Slotted, #1 and #2 Phillips, 1/4 In, 5/16 In, 7/16 In Nutdrivers, Ratcheting Screwdriver End, Ratcheting Wire Connector Wrench |
| Weight per unit | 0.7000 (lbs/each) |
| Product Category | Pliers, Wrenches, Saw, Pouches |

Features

| | |
|-------------|--|
| Handle Type | Textured, Ergonomic, Slip Resistant Comfort-Grip |
|-------------|--|

Material, Color, and Finish

| | |
|-----------------|-----------------|
| Blade Material | Chrome Vanadium |
| Handle Material | SANTOPRENE |

Descriptions

| | |
|------------------------|--|
| Description | RATCH-A-NUT 9-IN-1 SCREWDRIVER |
| extra long description | IDEAL 35-988 Screwdriver, Ideal, Ratch |
| Features | Patented Wire Connector Wrench accepts a wide variety of connectors and reduces finger fatigue. Pro-quality, 28 tooth, all metal ratchet can handle 225 lbs. of torque without failure. Ergonomic, slip-free textured grip provides excellent torque and is impervious to perspiration, gas, oil and chemicals. Accepts Twist-a-Nut replacement bits. Bits included: 1/4 in. Slotted, 3/16 in. Slotted, #1 Phillips, #2 Phillips, 1/4 in. Nutdriver, 5/16 in. Nutdriver, and 7/16 in. Nutdriver. Ratch-a-Nut 9-in-1 Screwdriver includes |
| Long Description | Ratch-a-Nut 9-In-1 Screwdriver, Textured, Ergonomic, Slip Resistant Comfort-Grip Handle, Santoprene Handle, Chrome Vanadium Blade, Includes: 1/4 IN And 3/16 IN Slotted, #1 And #2 Phillips, 1/4 IN, 5/16 IN, 7/16 IN Nutdrivers, Ratcheting Screwdriver End, Ratcheting Wire Connector Wrench |
| Product Type | Screwdriver, Ideal, Ratch-A-Nut |
| Special Features | Ratcheting wire connector wrench prevents finger fatigue and gets in tight spots; Premium screwdriver ratchet mechanism can handle high torque without failure; Ergonomic, slip resistant comfort-grip; Textured Santoprene grip provides excellent torque and resists perspiration, water, oil and chemicals; Accepts Twist-a-Nut replacement bits; Pro-quality, 28 tooth double action, twin-tooth ratchet; 225 LB of torque (stronger than human wrist can torque) |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250605224 |
| Manufacturers Part Number | 35-988 |
| UPC | 783250605224 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | HAND TOOLS |
| Type | 9-In-1 Screwdriver |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.7 |