



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



36301212 Encl 3X30X12 N12 PNTD CH Clamp CVR *Cooper B-Line/Cable Tray*

Catalog Number	36301212
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 36" Height, 12" Length, 30" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	85.1 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	12.0000 IN X 30.0000 IN X 36.0000 IN
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	30.00 In Width X 12.00 In Depth X 36.00 In Height
------	---------------------------------------------------

Descriptions

Description	ENCL 3X30X12 N12 PNTD CH CLAMP CVR
extra long description	B-LINE 363012-12 TYPE 12 SGL-DOOR E
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 36" height, 12" length, 30" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 36X30X12
Special Features	Plated door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051804508
Manufacturers Part Number	363012-12
UPC	782051804508

Taxonomies, Classifications, and Categories

Type	Type 12 panel enclosures
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	85.1

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherCommercial / Institutional Buildings / Structures - Power Distribution and ControlsDatacenters - IT Space: CI and Hyper ConvergedOther IT and Datacom - IT and Datacomm - OtherCommercial / Institutional Buildings / Structures - Safety and Security SystemsUtility - Substations, Utility Transmission and DistributionCommercial / Institutional Buildings /
Mounting standard	EXTERNAL FEET, WALL UL 508A, CSA C22.2., NEMA