



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 4075ST 3/4" STL Ins Throat *Appleton/Oz Gedney*

Catalog Number	4075ST
Manufacturer	Appleton/Oz Gedney
Description	Features:1 3/32IN Dia X 1 5/64IN Length, 7/16 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:0.75IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated, Insulation:Insulated Throat, Temperature Rating:90ce
Weight per unit	0.1300 (lbs/each)
Product Category	Steel Insulated Straight Set S

### Features

connection	Male NPS Thread
Connector Type	SET SCREW
insulation	Insulated Throat
Material	Steel

### Material, Color, and Finish

Color	Metallic
Finish	Zinc Electro Plated

### Dimensions and Weight

Size	0.75
------	------

### Descriptions

Description	3/4" STL INS THROAT
extra long description	EGS 4075ST 3/4 IN EMT SSCR CONN INS
Long Description	Features:1 3/32IN Dia X 1 5/64IN Length, 7/16 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:0.75IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated,Insulation:Insulated Throat, Temperature Rating:90CE
Product Type	3/4 In Emt SSCR Conn Insul Steel
Special Features	3/4 IN Trade Size Connector for EMT Conduit, Set Screw Type, Male Hub Threads NPS, Body Length 1.09 IN, Max. Dia. 1.08 IN,Thread Length 0.44IN, Concretetight when taped, Male Hub Threads - NPS, Insulated Throat

### Manufacturer Information

Brand	APPOZGCOMM
GTIN	00687855846085
Manufacturers Part Number	4075ST
UPC	687855846085



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	EMT Conduit Straight Set Screw Connector

## Trade Size

Trade Size	0.75
------------	------

## Packaging

Carton	20
Package	200
Weight Per each	0.13

## Uses, Certifications, and Standards

Application	To ground and secure EMT Raceways to boxes and enclosures
nema rating	FB-1
standard	UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard: C22.2 No. 18.3, cUL Listed: E14895, CSA Certified: 028507; NEMA: FB-1
Temperature Rating	90