



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



4150ST 1-1/2 In Emt SSCR Conn Insul Steel *Appleton/Oz Gedney*

Catalog Number	4150ST
Manufacturer	Appleton/Oz Gedney
Description	Features:1 15/16IN Dia X 1 15/16IN Length, 9/16 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:1.5IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated, Insulation:Insulated Throat, Temperature Rating:90C
Weight per unit	0.5000 (lbs/each)
Product Category	Steel Insulated Straight Set S

Features

connection	Male NPS Thread
Connector Type	SET SCREW
insulation	Insulated Throat
Material	Steel

Material, Color, and Finish

Color	Metallic
Finish	Zinc Electro Plated

Dimensions and Weight

Size	1.5
------	-----

Descriptions

Description	1-1/2 IN EMT SSCR CONN INSUL STEEL
extra long description	EGS 4150ST 1-1/2 IN EMT SSCR CONN I
Long Description	Features:1 15/16IN Dia X 1 15/16IN Length, 9/16 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:1.5IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated,Insulation:Insulated Throat, Temperature Rating:90C
Product Type	1-1/2 In Emt SSCR Conn Insul Steel
Special Features	1-1/2 IN Trade Size Connector for EMT Conduit, Set Screw Type, Male Hub Threads NPS, Body Length 1.94 IN, Max. Dia. 1.94 IN,Thread Length 0.56 IN, Concretetight when taped, Male Hub Threads - NPS, Insulated Throat

Manufacturer Information

Brand	Appleton/Oz Gedney
GTIN	00687855846238
Manufacturers Part Number	4150ST
UPC	687855846238



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Type EMT Conduit Straight Set Screw Connector

Trade Size

Trade Size 1.5

Packaging

Carton 1

Weight Per each 0.5

Uses, Certifications, and Standards

Application To ground and secure EMT Raceways to boxes and enclosures

nema rating FB-1

standard UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard:
C22.2 No. 18.3, cUL Listed: E14895, CSA Certified: 028507;
NEMA: FB-1

Temperature Rating 90