



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



4300ST 3 In Emt SSCR Conn Insul *Appleton/Oz Gedney*

Catalog Number	4300ST
Manufacturer	Appleton/Oz Gedney
Description	Features:2 1/2IN Dia X 4IN Length, 7/8 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:3IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated, Insulation:Insulated Throat, Temperature Rating:90ce
Weight per unit	1.6 (lbs/each)
Product Category	Steel Insulated Straight Set S

Features

connection	Male NPS Thread
Connector Type	SET SCREW
insulation	Insulated Throat
Material	Steel

Material, Color, and Finish

Color	Metallic
Finish	Zinc Electro Plated

Dimensions and Weight

Size	3
------	---

Descriptions

Description	3 IN EMT SSCR CONN INSUL
extra long description	EGS 4300ST 3 IN EMT SSCR CONN INSUL
Long Description	Features:2 1/2IN Dia X 4IN Length, 7/8 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:3IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated,Insulation:Insulated Throat, Temperature Rating:90CE
Product Type	3 In Emt SSCR Conn Insul Steel
Special Features	3 IN Trade Size Connector for EMT Conduit, Set Screw Type, Male Hub Threads NPS, Body Length 2.88 IN, Max. Dia. 3.75 IN,Thread Length 0.88 IN, Concretetight when taped, Male Hub Threads - NPS, Insulated Throat

Manufacturer Information

Brand	APPOZGCOMM
GTIN	00687855846375
Manufacturers Part Number	4300ST
UPC	687855846375



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	EMT Conduit Straight Set Screw Connector

Trade Size

Trade Size	3
------------	---

Packaging

Carton	5
Weight Per each	1.6

Uses, Certifications, and Standards

Application	To ground and secure EMT Raceways to boxes and enclosures
nema rating	FB-1
standard	UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard: C22.2 No. 18.3, cUL Listed: E14895, CSA Certified: 028507; NEMA: FB-1
Temperature Rating	90