



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



4350S 3-1/2'STL Set SCR Emt Conn *Appleton/Oz Gedney*

Catalog Number	4350S
Manufacturer	Appleton/Oz Gedney
Description	Features:2 1/2IN Dia X 4 1/2IN Length, 1 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:3.5IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated
Weight per unit	2.2 (lbs/each)
Product Category	Steel Uninsulated Straight Set

Features

connection	Male NPS Thread
Connector Type	SET SCREW
insulation	Not insulated
Material	Steel

Material, Color, and Finish

Color	Metallic
Finish	Zinc Electro Plated

Dimensions and Weight

Size	3.5
------	-----

Descriptions

Description	3-1/2'STL SET SCR EMT CONN
extra long description	EGS 4350S 3-1/2 IN EMT SSCR CONN
Long Description	Features:2 1/2IN Dia X 4 1/2IN Length, 1 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:3.5IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated
Product Type	3-1/2 In Emt SSCR Conn
Special Features	3-1/2 IN Trade Size Connector for EMT Conduit, Set Screw Type, Male Hub Threads NPS, Body Length 3.00 IN, Max. Dia. 4.25 IN,Thread Length 1.00 IN, Concretetight when taped, Male Hub Threads - NPS

Manufacturer Information

Brand	APPOZGCOMM
GTIN	00687855846382
Manufacturers Part Number	4350S
UPC	687855846382



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description STEEL EMT FITTINGS

Type EMT Conduit Straight Set Screw Connector

Trade Size

Trade Size 3.5

Packaging

Carton 5

Weight Per each 2.2

Uses, Certifications, and Standards

Application To ground and secure EMT Raceways to boxes and enclosures

nema rating FB-1

standard UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard:
C22.2 No. 18.3, cUL Listed: E14895, CSA Certified: 028507;
NEMA: FB-1