



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

240 VOLTS 240 VOLTS
240 VOLTS 240 VOLTS

44358 Voltage & Conduit Marker, "240V", Med, 4/Card

Ideal

Catalog Number	44358
Manufacturer	Ideal
Description	Ideal, Marker Card, Voltage and Conduit, Medium, Size: 1-1/8 In Width, Length: 4-1/2 In, Legend: 240V, Material: Vinyl-Impregnated Cloth, Temperature Range: -40 to 180 Deg F, Text Size: 3/4 In, Adhesion: 45 Oz/In Width Ultimate
Weight per unit	0.5000 (lbs/each)
Product Category	Markers & Marking Tapes

Features

Legend	240V
Material	Vinyl-Impregnated Cloth
Number of Markers	20

Dimensions and Weight

Length	4.5
Width	1-1/8

Descriptions

Description	VOLTAGE & CONDUIT MARKER, "240V", MED, 4/CARD
extra long description	IDEAL 44-358 Marker Card,Ideal,Volt
Features	Identify junction boxes, switches, circuit breakers, raceways, pipe and fuse boxesNon-conductive for user safetyHigh-adhesion properties with easy removabilityVinyl-impregnated cloth construction for long-lasting durabilityResist abrasion, moisture, dirt and oilNon-smear, black legend on bright orange background for high visibilityTemperature Range: -40°F to 180°F (-40°C to 82°C)Adhesion: 45 oz./in. width ultimate SELECT PART N
Long Description	IDEAL, Marker Card, Voltage And Conduit, Medium, Size: 1-1/8 IN Width, Length: 4-1/2 IN, Legend: 240V, Material: Vinyl-Impregnated Cloth, Temperature Range: -40 to 180 DEG F, Text Size: 3/4 IN, Adhesion: 45 OZ/IN Width Ultimate
Product Type	Voltage & Conduit Marker, "240V", Med, 4/Card
Special Features	Adhesion: 45 OZ/IN Width Ultimate;Features: Identify Junction Boxes, Switches, Circuit Breakers,Raceways, Pipe And Fuse Boxes;High-Adhesion Properties With Easy Removability;Non-Conductive For User Safety;Non-Smear, Black Legend On Bright Orange BackgroundFor High Visibility;Resist Abrasion, Moisture, Dirt And Oil;Temperature Range: -40 DEGF To 180 DEGF (-40 DEGC To 82 DEGC) Adhesion: 45 Oz/IN Width Ultimate;Temperature Range: -40 to 180 DEG F;Text Size: 3/4 IN;Vinyl-Impregnated Cloth Construction Provides



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Ideal
GTIN	00783250443581
Manufacturers Part Number	44-358
UPC	783250443581

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Voltage And Conduit, Medium

Packaging

Carton	25
Weight Per each	0.5

Uses, Certifications, and Standards

standard	RoHS
----------	------