



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



470FG 1-1/4" STL Cond Body CVR

Crouse-Hinds

Catalog Number	470FG
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Form 7 Wedge Nut Cover With Integral Gasket, Feraloy Iron Alloy, 1-1/4"
Weight per unit	0.7600 (lbs/each)
Product Category	Bodies & Covers

Features

dimensions	2.1800 IN X 0.8400 IN X 5.5000 IN
Material	FERALOY IRON ALLOY

Descriptions

Description	1-1/4" STL COND BODY CVR
extra long description	CRS-H 470FG 1 1/4 WDG NUT CST IRON F
Features	One hundred years after the introduction of the Condulet, Eaton remains the leader in conduit outlet bodies with its Crouse-Hinds series. The line has grown to six families manufactured in a variety of materials, and Form 7 bodies are offered in 11 different shapes to provide the most flexible offering on the market. Form 7 Condulet outlet bodies approach conduit in size for neat, compact installations. Many shapes and sizes are available for rigid threaded conduit. Our Form 7 family features an exclus
Long Description	Eaton Crouse-Hinds series Condulet Form 7 wedge nut cover with integral gasket, Feraloy iron alloy, 1-1/4"
Product Type	1 1/4 Wdgnut CST Iron Form 7 CVR/Gask
Special Features	With Neoprene Integral Gasket

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274233901
Manufacturers Part Number	470FG
UPC	782274233901

Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Wedge nut cover with integral gasket

Packaging

Carton	1
Package	10
Weight Per each	0.76



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D