



Catalog Number: 464-SC1  
Item Description: N1 SCREW COVER ENCL  
UPC Code: 784572107045




Brand Name: Milbank  
Type: Screw Cover  
Special Features: Cover Secured with Plated Screws  
Application: Enclosure for Mounting Electrical Equipment  
Standard: UL Listed  
Number Of Outlet: 0  
Material: Steel with Powder Coat Finish  
Color: ANSI 61 Gray  
Mounting: Wall Mount  
NEMA Rating: Type 1



*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

CATALOG NO.	LABEL NO.
464-SC1-( )	1002135
RC-464-SC1-( )	1125021
SPSC-644( )	1132714



ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK WELDMENT
2	1	(SEE CHART)	COVER PLATE
3	2	1001290	SCREW, 10-32 X 5/16
4	1	(SEE CHART)	LABEL (UL)
5	1	1002475	BAG ASSY (GROUND SCREW)
6	0.25	1002937	CARTON 4-PER (NOT SHOWN)



NOTES:

- 1.) BAG ASSY TO BE SHIPPED INSIDE OF ENCLOSURE.

SUFFIX	FINISH	WELDMENT NO.	COVER NO.	INSTALL KOs
NONE	MILBANK LIGHT GRAY	1160105	1160109	YES
-NP	NONE	1160107	1160110	
-NK	MILBANK LIGHT GRAY	1160106	1160109	NO
-NK-NP	NONE	1160108	1160110	

Material:	16 GA. STEEL	 <p>General Offices: Kansas City, MO</p>											
Shear/ Die#:													
Finish:	SEE CHART	Title:	SCREW COVER CAN 4 x 6 x 4 TYPE 1 ENCLOSURE										
Part Wt.:		Catalog No.:	SEE CHART										
<p>Tolerances:</p> <table border="0"> <tr><td>Unless Specified Otherwise</td><td></td></tr> <tr><td>X.X</td><td>±.1</td></tr> <tr><td>X.XX</td><td>±.03</td></tr> <tr><td>X.XXX</td><td>±.015</td></tr> <tr><td>X*</td><td>±2*</td></tr> </table>		Unless Specified Otherwise		X.X	±.1	X.XX	±.03	X.XXX	±.015	X*	±2*		
Unless Specified Otherwise													
X.X	±.1												
X.XX	±.03												
X.XXX	±.015												
X*	±2*												
Scale:	NTS	Checked By:											
Drawn By:	D.F.	Approved By:											
		Customer:	EALER ELECTRIC										
		Drawing No.:	1011144										
		Date:	7/24/12										
		Sheet	1 of 1										

NEMA DWG.: #102

REV.	DATE	DESCRIPTION	BY
E1	7/24/12	CHART VERSIONS (ECO #22677)	D.F.



Catalog Number: 464-SC1  
Item Description: N1 SCREW COVER ENCL  
UPC Code: 784572107045




Brand Name: Milbank  
Type: Screw Cover  
Special Features: Cover Secured with Plated Screws  
Application: Enclosure for Mounting Electrical Equipment  
Standard: UL Listed  
Number Of Outlet: 0  
Material: Steel with Powder Coat Finish  
Color: ANSI 61 Gray  
Mounting: Wall Mount  
NEMA Rating: Type 1



*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*



CATALOG NO.	LABEL NO.
464-SC1-( )	1002135
RC-464-SC1-( )	1125021
SPSC-644( )	1132714

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK WELDMENT
2	1	(SEE CHART)	COVER PLATE
3	2	1001290	SCREW, 10-32 X 5/16
4	1	(SEE CHART)	LABEL (UL)
5	1	1002475	BAG ASSY (GROUND SCREW)
6	0.25	1002937	CARTON 4-PER (NOT SHOWN)



NOTES:  
 1.) BAG ASSY TO BE SHIPPED INSIDE OF ENCLOSURE.

SUFFIX	FINISH	WELDMENT NO.	COVER NO.	INSTALL KOs
NONE	MILBANK LIGHT GRAY	1160105	1160109	YES
-NP	NONE	1160107	1160110	
-NK	MILBANK LIGHT GRAY	1160106	1160109	NO
-NK-NP	NONE	1160108	1160110	

Material:	16 GA. STEEL	 General Offices: Kansas City, MO
Shear/ Die#:		
Finish:	SEE CHART	
Part Wt.:		
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2*		Title: SCREW COVER CAN 4 x 6 x 4 TYPE 1 ENCLOSURE Catalog No.: SEE CHART Customer: EALER ELECTRIC Drawing No.: 1011144
Scale:	NTS	Third Angle 
Drawn By:	D.F.	Checked By: Approved By:
Date:		Date: 7/24/12 Sheet 1 of 1

NEMA DWG.: #102

REV.	DATE	DESCRIPTION	BY
E1	7/24/12	CHART VERSIONS (ECO #22677)	D.F.