



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



471LT12 3/4" 90D L/T Insul Throat Conn *Bridgeport Fittings*

| | |
|------------------|---|
| Catalog Number | 471LT12 |
| Manufacturer | Bridgeport Fittings |
| Description | Connector, Liquid Tight, Die Cast Zinc, Insulated Throat, Size 3/4 Inch |
| Weight per unit | 0.4620 (lbs/each) |
| Product Category | Liquid Tight Fittings |

Features

| | |
|----------------|-------------|
| angle | 90 DEG |
| Connector Type | Liquidtight |
| Material | Zinc Cast |
| media | Yes |

Material, Color, and Finish

| | |
|--------|--------------------|
| Finish | Zinc Electroplated |
|--------|--------------------|

Dimensions and Weight

| | |
|------|-----|
| Size | 3/4 |
|------|-----|

Descriptions

| | |
|------------------------|---|
| Description | 3/4" 90D L/T INSUL THROAT CONN |
| extra long description | BPT 471-LT12 3/4 LQDT.CONN.INS. 90 |
| Long Description | Connector, Liquid Tight, Die Cast Zinc, Insulated Throat, Size 3/4 Inch |
| Product Type | 3/4 LQDT.Conn.Ins. 90 Deg Zinc |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747164711 |
| Manufacturers Part Number | 471-LT12 |
| UPC | 781747164711 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------|
| Category Description | METALLIC FITTINGS |
| Type | CONNECTOR |

Trade Size

| | |
|------------|-----|
| Trade Size | 3/4 |
|------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.462 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

90 Degree connector for use with metallic and nonmetallic "Type B" liquid tight conduit. 3/8" thru 3/4" zinc die cast. Insulator rated 105 degree C.

standard

UL, CSA