



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48209105 3/16" X 2" X 4" Shockwave Carbide Hammer Drill Bit *Milwaukee Electric Tool*

Catalog Number	48209105
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee® Shockwave Impact Duty™ Carbide Hammer Drill Bits Are Designed With Sharpened Carbide to Deliver Up to 9X Longer Life and 4X Faster Drilling Into Concrete. Engineered With A Precision Ground Tip, These Bits Deliver Faster Starts and Less Walking In Concrete, Brick, and Block. Wide Flute Design Removes Dust Faster, Reducing Heat and Delivering More Holes Per Charge. Equipped With A 1/4" Hex Shank, Milwaukee® Shockwave Impact Duty™ Carbide Hammer Drill Bits Are The Ideal Solution For Drilling In
Weight per unit	0.0300 (lbs/each)
Product Category	Tools & Testers

Features

Flute Length	2
Material	Carbide
Shank Diameter	0.25

Dimensions and Weight

Length	4
Size	3/16



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	3/16" X 2" X 4" SHOCKWAVE CARBIDE HAMMER DRILL BIT
extra long description	MILW 48-20-9105 3/16" x 4" Hammer D
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	The MILWAUKEE® SHOCKWAVE Impact Duty™ Carbide Hammer Drill Bits are designed with sharpened carbide to deliver up to 9x longer life and 4x faster drilling into concrete. Engineered with a precision ground tip, these bits deliver faster starts and less walking in concrete, brick, and block. Wide flute design removes dust faster, reducing heat and delivering more holes per charge. Equipped with a ¼" Hex Shank, Milwaukee® SHOCKWAVE Impact Duty™ Carbide Hammer Drill Bits are the ideal solution for drilling in
Product Type	3/16" X 4" Hammer Drill Bit 25PK

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242546510
Manufacturers Part Number	48-20-9105
UPC	045242546510

Taxonomies, Classifications, and Categories

Category Description	TOOL BAG/POUCHES
Type	Hammer Drill Bit

Packaging

Carton	25
Package	400
Weight Per each	0.03