



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48322301 Shockwave 30 Knuckle Pivoting Bit Holder 11PC

Milwaukee Electric Tool

Catalog Number	48322301
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee® Shockwave™ Impact Duty™ 30° Knuckle™ Pivoting Bit Holder Allows Users to Drive Fasteners and Drill Holes In Tight, Difficult Work Areas. Its Innovative, Compact Design Locks At A 0° or 30° Angle and Is Designed For Use With Shockwave™ Impact Duty™ 1/4 In. Hex Accessories. It Is Rated to Handle Up to 2, 000 In-LBS Of Torque In Impact Drivers . The 30° Knuckle™ Is Engineered With Milwaukee® Shockwave™ Impact Duty™ Technology Which Is Built For Extreme Durability and Up to 10X Life. Made From Propri
Weight per unit	0.4700 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

idea granular category code	2413
Material	HEAT TREATED STEEL

Dimensions and Weight

Length	5.0
--------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	SHOCKWAVE 30 KNUCKLE PIVOTING BIT HOLDER 11PC
extra long description	MILW 48-32-2301 11-Piece Impact Knu
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	Milwaukee® SHOCKWAVE™ Impact Duty™ 30° knuckle™ pivoting bit holder allows users to drive fasteners and drill holes in tight, difficult work areas. Its innovative, compact design locks at a 0° or 30° angle and is designed for use with SHOCKWAVE™ Impact Duty™ 1/4 in. hex accessories. It is rated to handle up to 2,000 in-lbs of torque in impact drivers . The 30° knuckle™ is engineered with Milwaukee® SHOCKWAVE™ Impact Duty™ technology which is built for extreme durability and up to 10x life. Made from propri
Product Type	11-Piece Impact Knuckle Set
Special Features	Pivots to lock at a 0 - 30 DEG angle; Proprietary steel and heat treat process for maximum strength and durability; It is rated to handle up to 2, 000 LB-IN of torque in impact drivers; The 30 DEG Knuckle is engineered with Milwaukee SHOCKWAVE impact duty technology which is built for extreme durability and up to 10x life; Includes: (1) phillips Bit 1IN P1, (1) phillips Bit 1 IN P2, (1) phillips Bit 1 IN P3, (1) slotted Bit 1 IN SL 1/4 IN, (1) slotted Bit 1IN SL 1/8 IN, (1) slotted Bit 1 IN SL 3/16 IN, (1)

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242269587
Manufacturers Part Number	48-32-2301
UPC	045242269587

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	11-Piece Pivoting Bit Holder

Packaging

Carton	1
Weight Per each	0.47



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Use With Milwaukee SHOCKWAVE Impact Duty Insert

Magnetic Nut Drivers (1/4 IN, 5/16 IN, 3/8 IN, 7/16 IN, 1/2 IN)