



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48361612 Encl 48X36X16 N12 CH Clamp CVR

Cooper B-Line/Cable Tray

Catalog Number	48361612
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 48" Height, 16" Length, 36" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	135.9 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	16.0000 IN X 36.0000 IN X 48.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Descriptions

Description	ENCL 48X36X16 N12 CH CLAMP CVR
extra long description	B-LINE 483616-12 TYPE 12 SGL-DOOR E
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 48" height, 16" length, 36" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 48X36X16
Special Features	Plated door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051805208
Manufacturers Part Number	483616-12
UPC	782051805208

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 12 panel enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	135.9

Uses, Certifications, and Standards

Application	Other IT and Datacom - IT and Datacomm - OtherCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherGeneration - Renewable Energy - Alternative EnergyCommercial / Institutional Buildings / Structures - Critical PowerUtility - Substations, Utility Transmission and DistributionCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsDatacenters - IT Space: CI and Hyper ConvergedCommercial / Institutional Buildings / Structures -
Mounting	SURFACE
nema rating	12
standard	NEMA,CSA C22.2.,UL 508A