



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48892305 1/8" Cobalt Red Helix Drill Bit *Milwaukee Electric Tool*

Catalog Number	48892305
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee® Red Helix™ Cobalt 1/8" Drill Bit Is Engineered For Extreme Durability and Longer Life In Hard Metal Applications. The Milwaukee Cobalt Drill Bits Are Designed With A Variable Helix™ That Includes An Aggressive 35° Helix Angle Which Ends At 15°. The 135° Split Point Tip™ Delivers A Precision Start and Prevents Walking For Fast, Accurate Holes In Hard Metal, PVC and Wood. The Tapered Drill Bits Feature A New Enhanced Tapered Web™ That Strengthens The Bit'S Core to Increase Flute Durability. TH
Weight per unit	0.0150 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Drill Diameter	0.125
Flute Length	1.65
package quantity	1
Shank Diameter	0.125

Dimensions and Weight

Length	4.62
--------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	1/8" COBALT RED HELIX DRILL BIT
extra long description	MILW 48-89-2305 1/8 In. COBALT RED
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	The MILWAUKEE® RED HELIX™ Cobalt 1/8" Drill Bit is engineered for extreme durability and longer life in hard metal applications. The Milwaukee Cobalt drill bits are designed with a VARIABLE HELIX™ that includes an aggressive 35° Helix Angle which ends at 15°. The 135° SPLIT POINT TIP™ delivers a precision start and prevents walking for fast, accurate holes in Hard Metal, PVC and wood. The tapered drill bits feature a new ENHANCED TAPERED WEB™ that strengthens the bit's core to increase flute durability. Th
Product Type	1/8 In. Cobalt Red Helix
Short Description	1/8inCOBALT RED HELIX

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242188208
Manufacturers Part Number	48-89-2305
series	Milwaukee® Cobalt RED HELIX™ Drill Bits
UPC	045242188208

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

Packaging

Carton	1
Package	5
Weight	0.022
Weight Per each	0.015