



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48892309 3/16" Cobalt Red Helix Drill Bit *Milwaukee Electric Tool*

Catalog Number	48892309
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee® Red Helix™ Cobalt 3/16" Drill Bit Are Engineered For Extreme Durability and Longer Life In Hard Metal Applications. The Milwaukee Cobalt Drill Bits Are Designed With A Variable Helix™ That Includes An Aggressive 35° Helix Angle Which Ends At 15°. The Drill Bits Have Quadedge Tip™ to Decrease Heat Buildup and Drill Faster. The 135° Split Point Tip Delivers A Precision Start and Prevents Walking For Fast, Accurate Holes In Hard Metal, PVC and Wood. The Tapered Drill Bits Feature A New Enhance
Weight per unit	0.0300 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Drill Diameter	0.1880
Flute Length	2.360000
Grade	Heavy Duty
package quantity	1
Shank Diameter	0.187500

Dimensions and Weight

Length	5.62
--------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	3/16" COBALT RED HELIX DRILL BIT
extra long description	MILW 48-89-2309 3/16 In. COBALT RED
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	The MILWAUKEE® RED HELIX™ Cobalt 3/16" Drill Bit are engineered for extreme durability and longer life in hard metal applications. The Milwaukee Cobalt drill bits are designed with a VARIABLE HELIX™ that includes an aggressive 35° Helix Angle which ends at 15°. The drill bits have QUADEDGE TIP™ to decrease heat buildup and drill faster. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes in Hard Metal, PVC and wood. The tapered drill bits feature a new ENHANCE
Product Type	3/16 In. Cobalt Red Helix
Short Description	3/16inCOBALT RED HELIX

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242188246
Manufacturers Part Number	48-89-2309
series	Milwaukee® Cobalt RED HELIX™ Drill Bits
UPC	045242188246

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

Packaging

Carton	1
Package	275
Weight	0.030000
Weight Per each	0.03