



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## 48892309 3/16" Cobalt Red Helix Drill Bit

*Milwaukee Electric Tool*

|                  |  |
|------------------|--|
| Catalog Number   | 48892309   |
| Manufacturer     | Milwaukee Electric Tool  |
| Description      | The Milwaukee® Red Helix™ Cobalt 3/16" Drill Bit Are Engineered For Extreme Durability and Longer Life In Hard Metal Applications. The Milwaukee Cobalt Drill Bits Are Designed With A Variable Helix™ That Includes An Aggressive 35° Helix Angle Which Ends At 15°. The Drill Bits Have Quadedge Tip™ to Decrease Heat Buildup and Drill Faster. The 135° Split Point Tip Delivers A Precision Start and Prevents Walking For Fast, Accurate Holes In Hard Metal, PVC and Wood. The Tapered Drill Bits Feature A New Enhance |
| Weight per unit  | 0.0300 (lbs/each)  |
| Product Category | Bits, Parts, Accessories   |

### Features

|                  |            |
|------------------|------------|
| Drill Diameter   | 0.1880     |
| Flute Length     | 2.360000   |
| Grade            | Heavy Duty |
| package quantity | 1          |
| Shank Diameter   | 0.187500   |

### Dimensions and Weight

|        |      |
|--------|------|
| Length | 5.62 |
|--------|------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | 3/16" COBALT RED HELIX DRILL BIT   |
| extra long description | MILW 48-89-2309 3/16 In. COBALT RED  |
| Features               | MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening, |
| Long Description       | The MILWAUKEE® RED HELIX™ Cobalt 3/16" Drill Bit are engineered for extreme durability and longer life in hard metal applications. The Milwaukee Cobalt drill bits are designed with a VARIABLE HELIX™ that includes an aggressive 35° Helix Angle which ends at 15°. The drill bits have QUADEDGE TIP™ to decrease heat buildup and drill faster. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes in Hard Metal, PVC and wood. The tapered drill bits feature a new ENHANCE |
| Product Type           | 3/16 In. Cobalt Red Helix  |
| Short Description      | 3/16inCOBALT RED HELIX   |

## Manufacturer Information

|                           |   |
|---------------------------|---|
| Brand                     | Milwaukee®                              |
| GTIN                      | 00045242188246                          |
| Manufacturers Part Number | 48-89-2309                              |
| series                    | Milwaukee® Cobalt RED HELIX™ Drill Bits |
| UPC                       | 045242188246                            |

## Taxonomies, Classifications, and Categories

|                      |                             |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
|----------------------|-----------------------------|

## Packaging

|                 |          |
|-----------------|----------|
| Carton          | 1        |
| Package         | 275      |
| Weight          | 0.030000 |
| Weight Per each | 0.03     |