



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 48892729 23/64" Thunderbolt Black Oxide Drill Bit

Milwaukee Electric Tool

Catalog Number	48892729
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee® Thunderbolt® Black Oxide Jobber Length Drill Bits Are Designed For Extreme Durability and Long Life. The Thunderbolt Web Features A Thicker Core Than A Standard Drill Bit to Provide Ultimate Strength and Protect Against Side-Load Breakage. A Specially Designed Parabolic Flute Form Clears Chips Fast, While The 3-Flat Secure-Grip™ Shank Holds The Bit Firmly In The Drill Chuck. The 135° Split Point Tip Delivers A Precision Start and Prevents Walking For Fast, Accurate Holes. Effective For Drilling
Weight per unit	0.1100 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Drill Diameter	0.359
Flute Length	4.0
Grade	Heavy Duty
package quantity	1
Shank Diameter	0.25

### Dimensions and Weight

Length	6.0
--------	-----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	23/64" THUNDERBOLT BLACK OXIDE DRILL BIT
extra long description	MILW 48-89-2729 23/64" Thunderbolt
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	Milwaukee® Thunderbolt® Black Oxide jobber length drill bits are designed for extreme durability and long life. The Thunderbolt web features a thicker core than a standard drill bit to provide ultimate strength and protect against side-load breakage. A specially designed parabolic flute form clears chips fast, while the 3-Flat Secure-Grip™ shank holds the bit firmly in the drill chuck. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Effective for drilling
Product Type	23/64" Thunderbolt Black Oxide

## Manufacturer Information

Brand	Milwaukee®
GTIN	04524216700562
Manufacturers Part Number	48-89-2729
series	Milwaukee® Thunderbolt® Black Oxide
UPC	045242167005

## Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

## Packaging

Carton	1
Weight	0.11
Weight Per each	0.11