



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48892742 5/8" S&D Black Oxide Drill Bit

Milwaukee Electric Tool

Catalog Number	48892742
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee'S Thunderbolt® Silver & Deming Drill Bits Are Designed For Performance In Low to High Tensile Strength Materials, Stainless Steel and Cast Iron. Thunderbolt® Twist Drill Bits Are Made From Premium Industrial-Grade Steel With Heavy-Duty Cutting Surfaces That Power Through Deep or Shallow Holes With Lightning Speed. A Special Flute Geometry Adds Strength While Providing Increased Chip Ejection. Thunderbolt® Twist Drill Bits Have A Heavy Duty 135 Degree Split Point For Easy Penetration and A 1/2 In.
Weight per unit	0.3340 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Drill Diameter	0.625
Flute Length	4.0
Grade	Heavy Duty
package quantity	1
Shank Diameter	0.25

Dimensions and Weight

Length	6.0
--------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	5/8" S&D BLACK OXIDE DRILL BIT
extra long description	MILW 48-89-2742 5/8" S&D Black Oxid
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	Milwaukee's Thunderbolt® Silver & Deming drill bits are designed for performance in low to high tensile strength materials, stainless steel and cast iron. Thunderbolt® twist drill bits are made from premium industrial-grade steel with heavy-duty cutting surfaces that power through deep or shallow holes with lightning speed. A special flute geometry adds strength while providing increased chip ejection. Thunderbolt® twist drill bits have a heavy duty 135 degree split point for easy penetration and a 1/2 in.
Product Type	5/8" S&D Black Oxide Bit

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242167166
Manufacturers Part Number	48-89-2742
series	Milwaukee® S&D Black Oxide drill bits
UPC	045242167166

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

Packaging

Carton	1
Package	75
Weight	0.325
Weight Per each	0.334