



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48899244 Shockwave Impact Duty #4 3/16 - 7/8"

Milwaukee Electric Tool

Catalog Number	48899244
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee®'S Shockwave™ Impact Duty™ Step Bits Are Engineered to Deliver The Most Durable and Fastest Holes In The Market. Made In The Usa With Global Materials, These Step Bits Have Best-In-Class Performance In Impact Drivers and The Versatility to Be Used In Drills. The 1/4 In. Hex Shank With An Optimized Shockzone™ Provide The Industry'S Most Durable Shank, Reducing Early Shank Breaks. A Titanium Aluminum Nitride (Tibone) Coating Helps Deliver 5X Longer Life, While The Rapid Strike™ Tip and Dual Spiral
Weight per unit	0.2200 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Flute Length	1.949
Shank Diameter	0.25

Dimensions and Weight

Length	3.584
--------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	SHOCKWAVE IMPACT DUTY #4 3/16 - 7/8"
extra long description	MILW 48-89-9244 Step Bit #4 3/16 -
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	Milwaukee®'s SHOCKWAVE™ Impact Duty™ step bits are engineered to deliver the most durable and fastest holes in the market. Made in the USA with global materials, these step bits have best-in-class performance in impact drivers and the versatility to be used in drills. The 1/4 in. hex shank with an optimized Shockzone™ provide the industry's most durable shank, reducing early shank breaks. A titanium aluminum nitride (TiBone) coating helps deliver 5x longer life, while the Rapid Strike™ tip and dual spiral
Product Type	Step Bit #4 3/16 - 7/8 In.
Short Description	Step Bit #4 3/16 - 7/8 in.

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242505081
Manufacturers Part Number	48-89-9244
UPC	045242505081

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

Packaging

Carton	1
Package	128
Weight Per each	0.22