



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



49240146 M12 Work Light

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 49240146 |
| Manufacturer | Milwaukee Electric Tool |
| Description | The M12™ Cordless Led Work Light Outlasts and Outperforms All Other Subcompact Lights. Powered By An M12™ Red Lithium™ Battery, The Work Light Is 2X Brighter and Whiter Than Conventional Incandescent Bulbs and Runs Up to Twice As Long. With A Sealed Aluminum Head to Provide Impact and Weather Resistance, Milwaukee® Provides A Limited Lifetime Led Warranty. A Magnetic Back Allows Hands-Free Use While A 90 Degree Rotating Head Allows The User to Easily Point The Light Beam At The Desired Work Area. |
| Weight per unit | 0.7400 (lbs/each) |
| Product Category | Worklight Lighting |

Features

| | |
|-----------------|-----------------|
| battery | Lithium-Ion |
| Battery Size | Battery Packs |
| Battery Voltage | 12 |
| bulb type | LED |
| charge time | 0.5 |
| lumens | 160 |
| Material | Rugged Overmold |
| Voltage Rating | 12 |
| Water Resistant | NO |

Material, Color, and Finish

| | |
|-------------------|------|
| color temperature | 5600 |
|-------------------|------|

Dimensions and Weight

| | |
|------|-----------------|
| Size | 8.500 IN Length |
|------|-----------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | M12 WORK LIGHT |
| extra long description | MILW 49-24-0146 12V LED WORKLIGHT |
| Features | M12™ Cordless LED Work Light |
| Long Description | The M12™ cordless LED work light outlasts and outperforms all other subcompact lights. Powered by an M12™ Red Lithium™ battery, the work light is 2X brighter and whiter than conventional incandescent bulbs and runs up to twice as long. With a sealed aluminum head to provide impact and weather resistance, Milwaukee® provides a limited lifetime LED warranty. A magnetic back allows hands-free use while a 90 degree rotating head allows the user to easily point the light beam at the desired work area. |
| Product Type | 12V Led Worklight |
| Short Description | 12V LED WORKLIGHT |
| Special Features | Features: Aluminum Head Impact And Weather Resistant; 90 DEG Rotating Head Aims Light At Work Space; Magnetic Back Hands-Free Use; M12 Works With Milwaukee 12 V Redlithium Battery Pack; Tool Weight: 0.900 LB |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242188604 |
| Manufacturers Part Number | 49-24-0146 |
| UPC | 045242188604 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | FLASHLIGHTS AND BATTERIES |
| Type | Cordless, LED |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.74 |