



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



49251131 Open-Lok 1-3/8" HCS Hardwood Blade

Milwaukee Electric Tool

| | |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | 49251131 |
| Manufacturer | Milwaukee Electric Tool |
| Description | The Milwaukee® Open-Lok™ 1-3/8" HCS Japanese Tooth Pro-Curve™ Hardwood Oscillating Multi-Tool Blades Are Made From Premium High Carbon Steel and Feature Precision Triple-Ground Japanese Teeth For Up to 2X Faster Cuts Than The Previous Generation Of High Carbon Steel Blades. The Japanese Tooth Hardwood Blades Have A Pro-Curve™ Cutting Edge For Greater Control and Accuracy While Cutting. The Combination Of Japanese Teeth and Pro-Curve™ Cutting Edge Make This Blade The Optimal Solution For Precise Cuts With A |
| Weight per unit | 0.0800 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|-----------------|-------|
| Blade Length | 2.05 |
| Blade Thickness | 0.025 |
| Teeth per Inch | 18 |

Dimensions and Weight

| | |
|------|-------|
| Size | 1-3/8 |
|------|-------|

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | OPEN-LOK 1-3/8" HCS HARDWOOD BLADE |
| extra long description | MILW 49-25-1131 1-3/8" HCS JAPANESE |
| Features | MILWAUKEE® Oscillating Multi-Tool Accessories provide a complete solution for cutting, scraping, sanding and grinding across a wide range of materials and applications. Equipped with an OPEN-LOK™ Universal blade anchor for quick blade changes. Made with high quality materials and advanced manufacturing processes to deliver professional grade performance and market leading innovation. |
| Long Description | The MILWAUKEE® OPEN-LOK™ 1-3/8" HCS Japanese Tooth PRO-CURVE™ Hardwood Oscillating Multi-Tool Blades are made from premium high carbon steel and feature precision triple-ground Japanese teeth for up to 2X faster cuts than the previous generation of high carbon steel blades. The Japanese Tooth hardwood blades have a PRO-CURVE™ cutting edge for greater control and accuracy while cutting. The combination of Japanese Teeth and PRO-CURVE™ cutting edge make this blade the optimal solution for precise cuts with a |
| Product Type | 1-3/8" HCS Japanese Tooth Blade 1PK |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242570829 |
| Manufacturers Part Number | 49-25-1131 |
| UPC | 045242570829 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
| Type | Multi-Tool Blade |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 4 |
| Weight Per each | 0.08 |

Uses, Certifications, and Standards

| | |
|-------------|--------------|
| Application | HCS Hardwood |
|-------------|--------------|