



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 49251201 Open-Lok 3/8" Titanium Enhanced Bi-Metal Blade

*Milwaukee Electric Tool*

|                  |   |
|------------------|---|
| Catalog Number   | 49251201  |
| Manufacturer     | Milwaukee Electric Tool   |
| Description      | The Milwaukee® Open-Lok™ 3/8" Titanium Charged™ Bi-Metal Multi-Material Oscillating Multi-Tool Blades Are Made From Premium High-Speed Steel. These Bi-Metal Blades Are Ideal For Cuts In Wood, Nails, PVC, and Drywall. Titanium Charged™ Bi-Metal Blades Have An Optimized Titanium Blend For Maximum Wear-Resistance and Up to 15X Longer Life VS. High Carbon Steel (HCS) Blades. These Blades Feature A Reinforced Universal Fit Open-Lok™ Anchor For Better Strength & Control and Allow For Quick Blade Changes Across 1 |
| Weight per unit  | 0.0800 (lbs/each)   |
| Product Category | Tools & Testers   |

### Features

|                 |       |
|-----------------|-------|
| Blade Length    | 2.67  |
| Blade Thickness | 0.025 |
| Teeth per Inch  | 18    |

### Dimensions and Weight

|      |     |
|------|-----|
| Size | 3/8 |
|------|-----|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | OPEN-LOK 3/8" TITANIUM ENHANCED BI-METAL BLADE  |
| extra long description | MILW 49-25-1201 3/8" TITANIUM BI-ME   |
| Features               | MILWAUKEE® Oscillating Multi-Tool Accessories provide a complete solution for cutting, scraping, sanding and grinding across a wide range of materials and applications. Equipped with an OPEN-LOK™ Universal blade anchor for quick blade changes. Made with high quality materials and advanced manufacturing processes to deliver professional grade performance and market leading innovation.  |
| Long Description       | The MILWAUKEE® OPEN-LOK™ 3/8" TITANIUM CHARGED™ Bi-Metal Multi-Material Oscillating Multi-Tool Blades are made from premium high-speed steel. These bi-metal blades are ideal for cuts in wood, nails, PVC, and drywall. TITANIUM CHARGED™ Bi-Metal blades have an optimized titanium blend for maximum wear-resistance and up to 15x longer life vs. high carbon steel (HCS) blades. These blades feature a reinforced Universal Fit OPEN-LOK™ anchor for better strength & control and allow for quick blade changes across 1 |
| Product Type           | 3/8" Titanium Bi-Metal Blade 1PK  |
| Short Description      | 3/8" Titanm BI-METAL Bld 1PK  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Milwaukee®     |
| GTIN                      | 00045242570911 |
| Manufacturers Part Number | 49-25-1201     |
| UPC                       | 045242570911   |

## Taxonomies, Classifications, and Categories

|                      |                             |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
| Type                 | Multi-Tool Blade            |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 4    |
| Weight Per each | 0.08 |

## Uses, Certifications, and Standards

|             |                |
|-------------|----------------|
| Application | Multi-Material |
|-------------|----------------|