



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 49251233 Open-Lok 1-3/8" Titanium Charged Bi-Metal Multi-Ma *Milwaukee Electric Tool*

Catalog Number	49251233
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee® Open-Lok™ 1-3/8" Titanium Charged™ Bi-Metal Multi-Material Oscillating Multi-Tool Blades Are Made From Premium High-Speed Steel. These Bi-Metal Blades Are Ideal For Cuts In Wood, Nails, PVC, and Drywall. Titanium Charged™ Bi-Metal Blades Have An Optimized Titanium Blend For Maximum Wear-Resistance and Up to 15X Longer Life VS. High Carbon Steel (HCS) Blades. These Blades Feature A Reinforced Universal Fit Open-Lok™ Anchor For Better Strength & Control and Allow For Quick Blade Changes Across
Weight per unit	0.1900 (lbs/each)
Product Category	Tools & Testers

### Features

Blade Thickness	0.025
blade type	Multi-Tool

### Material, Color, and Finish

Blade Material	High Carbon Steel
----------------	-------------------

### Dimensions and Weight

Size	1-3/8
------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	OPEN-LOK 1-3/8" TITANIUM CHARGED BI-METAL MULTI-MA
extra long description	MILW 49-25-1233 1-3/8" TITANIUM BI-
Features	MILWAUKEE® Oscillating Multi-Tool Accessories provide a complete solution for cutting, scraping, sanding and grinding across a wide range of materials and applications. Equipped with an OPEN-LOK™ Universal blade anchor for quick blade changes. Made with high quality materials and advanced manufacturing processes to deliver professional grade performance and market leading innovation.
Long Description	The MILWAUKEE® OPEN-LOK™ 1-3/8" TITANIUM CHARGED™ Bi-Metal Multi-Material Oscillating Multi-Tool Blades are made from premium high-speed steel. These bi-metal blades are ideal for cuts in wood, nails, PVC, and drywall. TITANIUM CHARGED™ Bi-Metal blades have an optimized titanium blend for maximum wear-resistance and up to 15x longer life vs. high carbon steel (HCS) blades. These blades feature a reinforced Universal Fit OPEN-LOK™ anchor for better strength & control and allow for quick blade changes across
Product Type	1-3/8" Titanium Bi-Metal Blades 3PK

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242570973
Manufacturers Part Number	49-25-1233
UPC	045242570973

## Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Multi-Tool Blades

## Packaging

Carton	1
Package	4
Weight Per each	0.19

## Uses, Certifications, and Standards

Application	Multi-Material
-------------	----------------