



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



4D22SH120GLV BLTD 4D Galv Strut 2-1/8"X2-1/8"(Deep)

Cooper B-Line/Cable Tray

Catalog Number	4D22SH120GLV
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series 4DIMENSION Strut Channel, 2.12" Channel Height, 120" Channel Length, 2.12" Channel Width, 18 Gauge Steel, SH Hole Pattern, 4D22 Channel Type, Pre-Galvanized
Weight per unit	1.6 (lbs/each)
Product Category	Channel & Strut

Material, Color, and Finish

Finish	Pre-Galvanized
--------	----------------

Dimensions and Weight

Length	120 in
Width	2.106 IN

Descriptions

Also Known As...	Strut Strut channel
Description	BLTD 4D GALV STRUT 2-1/8"X2-1/8"(DEEP)
extra long description	B-LINE 4D22SH-120GLV 4D CHNL, 2" X
Features	Eaton's 4Dimension strut system features revolutionary strut profile designs and innovative accessories that help installers compress project schedules and cut costs without sacrificing load. With four-sided functionality, the 4Dimension strut system delivers up to 50% savings on materials and installation time. Eaton's 4Dimension strut system changes how installers build and install support systems for electrical, mechanical, plumbing, data centers, and HVAC in new and retrofit commercial and industrial ap
Long Description	Eaton B-Line series 4Dimension strut channel, 2.12" channel height, 120" channel length, 2.12" channel width, 18 Gauge steel, SH hole pattern, 4D22 channel type, Pre-galvanized
Product Type	4D CHNL, 2" X 2", 5/8" X 1 1/4" Slotted Holes, 18 Ga, 120-
similar brands	Unistrut

Manufacturer Information

Brand	Eaton
GTIN	00799038582984
Manufacturers Part Number	4D22SH120GLV
UPC	799038582984



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description STRUT CHANNEL

Type Strut channel

Availability

minimum qty 10

Status Inactive

Packaging

Carton 10

Package 320

Weight 1.548 LB/PER FT

Weight Per foot 1.603

Uses, Certifications, and Standards

standard Not Applicable