




4G16 TWIST CLIP WITH WING NUT, SPRING STEEL, NVENT CADDY ARMOUR, 0.563" SCREW

CATALOG NUMBER

4G16



CERTIFICATIONS



FEATURES

Supports electrical fixtures from acoustical T-grid

No tools required for installation

Fast, easy and secure twist-on installation

Wing nut included

PRODUCT ATTRIBUTES

Material: Spring Steel

Finish: nVent CADDY Armour

T-Grid Size: 15/16"

Screw Diameter: 1/4"

Screw Length: 9/16"

Static Load: 50lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500




Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER



4G16 TWIST CLIP WITH WING NUT, SPRING STEEL, NVENT CADDY ARMOUR, 0.563" SCREW

CATALOG NUMBER

4G16



CERTIFICATIONS



FEATURES

Supports electrical fixtures from acoustical T-grid

No tools required for installation

Fast, easy and secure twist-on installation

Wing nut included

PRODUCT ATTRIBUTES

Material: Spring Steel

Finish: nVent CADDY Armour

T-Grid Size: 15/16"

Screw Diameter: 1/4"

Screw Length: 9/16"

Static Load: 50lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER