



## LAY-IN AND TROFFER SUPPORT CLIP, STRAIGHT/UPTURNED LIP

### CATALOG NUMBER

---

**515A**



### CERTIFICATIONS

---



### FEATURES

---

Provides a positive method for securing troffers, lay-ins, and air diffusers

### PRODUCT ATTRIBUTES

---

Material: Spring Steel

Finish: GEOMET® 321

Complies With: NEC® Article 410.36

### ADDITIONAL PRODUCT DETAILS

---

No load rating, for positioning only.

### WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation,

misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**



## LAY-IN AND TROFFER SUPPORT CLIP, STRAIGHT/UPTURNED LIP

### CATALOG NUMBER

---

**515A**



### CERTIFICATIONS

---



### FEATURES

---

Provides a positive method for securing troffers, lay-ins, and air diffusers

### PRODUCT ATTRIBUTES

---

Material: Spring Steel

Finish: GEOMET® 321

Complies With: NEC® Article 410.36

### ADDITIONAL PRODUCT DETAILS

---

No load rating, for positioning only.

### WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation,

misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**